

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Test Adapters

## General Information

<b>Extended Product Type:</b>	TP2
<b>Product ID:</b>	1SNK900203R0000
<b>EAN:</b>	3472599097315
<b>Catalog Description:</b>	TP2 Test Adapter for test plugs DIA 2 mm .079 in - Dark Grey
<b>Long Description:</b>	- Insulated test adapter that enables individual voltage control, - Direct plug-in solution into the jumpers channels, - Compatible with standard isolated or non isolated test plugs DIA 2 mm 0.079 in and 2.3 mm 0.090 in, - With stand more than 10000 operations according to ABB test standards.

## Ordering

<b>Color:</b>	Dark Grey
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160036D0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	7.6 mm
<b>Product Net Height:</b>	7.6 mm
<b>Product Net Length:</b>	52.15 mm
<b>Product Net Depth / Length:</b>	52.2 mm
<b>Product Net Weight:</b>	1.7 g

## Technical

<b>Spacing:</b>	7.6 mm
<b>Function:</b>	Test Adapters
<b>Rated Current (<math>I_n</math>):</b>	Main Circuit 10 A
<b>Rated Short-time Withstand Current (<math>I_{cw}</math>):</b>	for 1 s 60 A
<b>Rated Voltage (<math>U_r</math>):</b>	1000 V
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	8000 V
<b>Dielectric Test Voltage:</b>	2200 V

<b>Pollution Degree:</b>	3
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Suitable For:</b>	ZDK2.5-22 ZDK4-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZDS4-22-R1 ZK10 ZK10-3P ZK10-PE ZK10-PE-3P ZK16 ZK16-3P ZK16-PE ZK16-PE-3P ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-CH-4P ZK2.5-D1 ZK2.5-D1-PE ZK2.5-D2 ZK2.5-D2-PE ZK2.5-D-CH ZK2.5-PE ZK2.5-PE-3P ZK2.

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Flammability According to UL94:</b>	V0

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Instructions and Manuals:</b>	1SNK160027C0201
----------------------------------	-----------------

RoHS Information:

1SND230505F0202

## Classifications

Object Classification Code: X

E-nummer: 2925155

## Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 158 mm

Package Level 1 Depth / Length: 243 mm

Package Level 1 Gross Weight: 0.034 kg

Package Level 1 EAN: 3472599097315

Package Level 2 Units: 2000 piece

Product Packing Type: Bag

