

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Test Adapters

General Information

Extended Product Type:	TP4
Product ID:	1SNK900205R0000
EAN:	3472599097322
Catalog Description:	TP4 Test Adapter for test plugs DIA 4 mm .16 in - Dark Grey
Long Description:	- Isolated test adapter that enables individual voltage control, - Direct plug-in solution into the jumpers channels, - Compatible with standard insulated or non isolated test plugs DIA 4 mm 0.157 in, - Withstand more than 10000 operations according to ABB test standards.

Ordering

Color:	Dark Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160036D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	7.6 mm
Product Net Height:	7.6 mm
Product Net Length:	56.63 mm
Product Net Depth / Length:	56.6 mm
Product Net Weight:	2.4 g

Technical

Spacing:	7.6 mm
Function:	Test Adapters
Rated Current (I_n):	Main Circuit 16 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Insulation Material: Polyamide

Suitable For: ZDK2.5-22
ZDK4-22
ZDP2.5-11
ZDP2.5-22
ZDP2.5-D1
ZDP2.5-D2
ZDS4-22
ZDS4-22-R1
ZK10
ZK10-3P
ZK10-PE
ZK10-PE-3P
ZK16
ZK16-3P
ZK16-PE
ZK16-PE-3P
ZK2.5
ZK2.5-3P
ZK2.5-4P
ZK2.5-CH-4P
ZK2.5-D1
ZK2.5-D1-PE
ZK2.5-D2
ZK2.5-D2-PE
ZK2.5-D-CH
ZK2.5-PE
ZK2.5-PE-3P
ZK2.

Technical UL/CSA

Maximum Operating Voltage Main Circuit 600 V
UL/CSA:

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230505F0202

Classifications

Object Classification Code: X

E-nummer: 2925156

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 158 mm

Package Level 1 Depth / Length: 243 mm

Package Level 1 Gross Weight: 0.048 kg

Package Level 1 EAN: 3472599097322

Package Level 2 Units: 2000 piece

Product Packing Type: Bag

