

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Component Plugs

General Information

Extended Product Type:	PG5
Product ID:	1SNK900401R0000
EAN:	3472599097339
Catalog Description:	PG5 Component Plug - Dark Grey
Long Description:	- Ease the components installation (components not supplied with plug) with our quick plug-in mounting system which avoids soldering process, - Accept 8.8 x 3.2 mm 0.346 x 0.125 in components such as resistors, diodes or subminiature fuses (fully encapsulated), - Maximum dissipated power: 1 W.

Ordering

Color:	Dark Grey
---------------	-----------

Minimum Order Quantity:	20 piece
--------------------------------	----------

Customs Tariff Number:	85369010
-------------------------------	----------

Popular Downloads

Data Sheet, Technical Information:	1SNK160038D0201
---	-----------------

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	5.2 mm
---------------------------	--------

Product Net Height:	31 mm
----------------------------	-------

Product Net Length:	39 mm
----------------------------	-------

Product Net Depth / Length:	39 mm
------------------------------------	-------

Product Net Weight:	3.5 g
----------------------------	-------

Technical

Spacing:	5.2 mm
-----------------	--------

Function:	Component Plugs
------------------	-----------------

Rated Voltage (U_r):	400 V
---------------------------------------	-------

Rated Impulse Withstand Voltage (U_{imp}):	6000 V
---	--------

Dielectric Test Voltage:	1890 V
---------------------------------	--------

Pollution Degree:	3
--------------------------	---

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

Insulation Material:	Polyamide
Suitable For:	ZK2.5-SP ZK2.5-SP-4P ZP2.5-SP ZS10-S ZS10-SP ZS4-SP ZS4-SP-R1 ZS4-SP-T2 ZS4-SP-T2-R1

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 150 V
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230496F0202

Classifications

Object Classification Code:	X
E-nummer:	2925157
ETIM 4:	EC002018 - Component plug terminal block
ETIM 5:	EC002018 - Component plug terminal block
ETIM 6:	EC002018 - Component plug terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	170 mm
Package Level 1 Depth / Length:	125 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.07 kg
Package Level 1 EAN:	3472599097339
Package Level 2 Units:	1000 piece

Package Level 2 Width:	200 mm
Package Level 2 Depth / Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	96000 piece
Product Packing Type:	Bag

