

SC-JB8-3-OR



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Short Circuit Bridges

General Information

Extended Product Type:	SC-JB8-3-OR
Product ID:	1SNK900657R0000
EAN:	3472599857490
Catalog Description:	SC-JB8-3 Short circuit bridges - Orange
Long Description:	- Allow safe short-circuiting of Current Transformers circuits, - Insulated, - Fully operated by screwdriver, - Short circuited fixed position secured thanks to AJS9 tightening, - Adapted hook shape maintains the bridge on the terminal block in the non short-circuited position, - The orange version can be used as fixed jumpers.

Ordering

Color:	Orange
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85389099

Popular Downloads

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	8 mm
---------------------------	------

Technical

Spacing:	8 mm
Function:	Short Circuit Bridges
Rated Current (I_n):	Main Circuit 5 A
Insulation Material:	Polyamide
Suitable For:	ZS10-PE-R1 ZS10-R1 ZS10-ST ZS10-ST-T4

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

RoHS Status:

Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230528F0200

Classifications

Object Classification Code: X

Container Information

Package Level 1 Units: 25 piece

Package Level 1 Width: 125 mm

Package Level 1 Depth / Length: 170 mm

Package Level 1 Height: 20 mm

Package Level 1 Gross Weight: 0.085 kg

Package Level 1 EAN: 3472599857490

Package Level 2 Units: 500 piece

Package Level 2 Width: 175 mm

Package Level 2 Depth / Length: 227 mm

Package Level 2 Height: 130 mm

Package Level 2 Gross Weight: 1.7 kg

Package Level 3 Units: 24000 piece

