

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	JB12-2
Product ID:	1SNK912302R0000
EAN:	3472599123021
Catalog Description:	JB12-2 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

Ordering

Color:	Orange
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160027C0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	12 mm
Product Net Height:	20 mm
Product Net Depth / Length:	31.5 mm
Product Net Weight:	4.9 g

Technical

Spacing:	12 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 76 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

Suitable For:	ZK16
	ZK16-3P
	ZK16-PE
	ZK16-PE-3P
	ZS25
	ZS25-PE

Technical UL/CSA

Maximum Operating Voltage	Main Circuit 600 V
UL/CSA:	

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
	Storage -55 ... +110 °C

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

RoHS Information:	1SND230491F0206
--------------------------	-----------------

Classifications

Object Classification Code:	X
------------------------------------	---

Container Information

Package Level 1 Units:	50 piece
-------------------------------	----------

Package Level 1 Width:	45 mm
-------------------------------	-------

Package Level 1 Depth / Length:	105 mm
--	--------

Package Level 1 Height:	45 mm
--------------------------------	-------

Package Level 1 Gross Weight:	0.293 kg
--------------------------------------	----------

Package Level 1 EAN:	3472599123021
-----------------------------	---------------

Package Level 2 Units:	1500 piece
-------------------------------	------------

Package Level 2 Width:	200 mm
-------------------------------	--------

Package Level 2 Depth / Length:	200 mm
--	--------

Package Level 2 Height:	300 mm
--------------------------------	--------

Package Level 3 Units:	96000 piece
-------------------------------	-------------

Product Packing Type:	Box
------------------------------	-----

