

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

Extended Product Type:	JB22-5
Product ID:	1SNK922305R0000
EAN:	3472599163621
Catalog Description:	JB22-5 Jumper Bar
Long Description:	Screw jumper bars

## Ordering

Minimum Order Quantity:	5 piece
Customs Tariff Number:	85369010

## Popular Downloads

Data Sheet, Technical Information:	1SNK160033D0201
Instructions and Manuals:	1SNK160027C0201

## Dimensions

Product Net Width:	22 mm
Product Net Height:	101 mm
Product Net Length:	20.7 mm
Product Net Depth / Length:	20.7 mm
Product Net Weight:	76.1 g

## Technical

Spacing:	22 mm
Function:	Jumper Bars
Rated Current ( $I_n$ ):	Main Circuit 192 A
Rated Short-time Withstand Current ( $I_{cw}$ ):	for 1 s 8400 A
Rated Voltage ( $U_r$ ):	1000 V
Rated Impulse Withstand Voltage ( $U_{imp}$ ):	8000 V
Dielectric Test Voltage:	2200 V
Power Loss:	6.1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

<b>Recommended Screw Driver:</b>	4 mm
<b>Suitable For:</b>	D70/22 ZS70

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
--	--------------------

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>ATEX Certificate:</b>	1SND162004A1708
<b>CB Certificate:</b>	1SND161034A0202
<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>RoHS Information:</b>	1SND230499F0202

## Classifications

<b>Object Classification Code:</b>	X
<b>E-nummer:</b>	2925395
<b>ETIM 4:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 6:</b>	EC000489 - Cross-connector for terminal block

## Container Information

<b>Package Level 1 Units:</b>	5 piece
<b>Package Level 1 Width:</b>	45 mm
<b>Package Level 1 Depth / Length:</b>	105 mm
<b>Package Level 1 Height:</b>	45 mm
<b>Package Level 1 Gross Weight:</b>	0.38 kg
<b>Package Level 1 EAN:</b>	3472599163621
<b>Package Level 2 Units:</b>	105 piece
<b>Package Level 2 Width:</b>	200 mm
<b>Package Level 2 Depth / Length:</b>	300 mm
<b>Package Level 2 Height:</b>	200 mm
<b>Package Level 2 Gross Weight:</b>	8.23 kg
<b>Package Level 3 Units:</b>	10080 piece
<b>Product Packing Type:</b>	Box

