

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Female Plugs

General Information

Extended Product Type:	L26520611000
Product ID:	1SSA265206R1100
EAN:	3472599034464
Catalog Description:	FIC F ADO 6P/5.08 Female Plugs
Long Description:	ADO plugs allow connection of 2 wires of the same size and nature.

Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	11 g
----------------------------	------

Technical

Rated Cross-Section:	1 mm ²
Spacing:	5.08 mm
Connection Type:	ADO System
Function:	Female Plugs
Rated Current (I_n):	Main Circuit 13.5 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 120 A
Rated Voltage (U_r):	500 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity UL/CSA:	Stranded 16 AWG

Certificates and Declarations (Document Number)

cUL Certificate:	1SND163008A0200
Declaration of Conformity - CE:	1SSD235020C1002

Classifications

Object Classification Code:	X
ETIM 4:	EC002638 - Cable connector
ETIM 5:	EC002638 - Cable connector
ETIM 6:	EC002638 - Cable connector

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	101 mm
Package Level 1 Depth / Length:	220 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.55 kg
Package Level 1 EAN:	3472599034464
Package Level 2 Units:	500 piece
Package Level 3 Units:	24000 piece
Product Packing Type:	Box

