

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Female Plugs

## General Information

|                               |                                                                    |
|-------------------------------|--------------------------------------------------------------------|
| <b>Extended Product Type:</b> | L26620211000                                                       |
| <b>Product ID:</b>            | 1SSA266202R1100                                                    |
| <b>EAN:</b>                   | 3472599285378                                                      |
| <b>Catalog Description:</b>   | FIC F ADO 2P/7.62 T01 STD Female Plugs                             |
| <b>Long Description:</b>      | ADO plugs allow connection of 2 wires of the same size and nature. |

## Ordering

|                                |          |
|--------------------------------|----------|
| <b>Color:</b>                  | Grey     |
| <b>Minimum Order Quantity:</b> | 50 piece |
| <b>Customs Tariff Number:</b>  | 85369010 |

## Dimensions

|                            |     |
|----------------------------|-----|
| <b>Product Net Weight:</b> | 6 g |
|----------------------------|-----|

## Technical

|                                                             |                                                              |
|-------------------------------------------------------------|--------------------------------------------------------------|
| <b>Rated Cross-Section:</b>                                 | 1.5 mm <sup>2</sup>                                          |
| <b>Spacing:</b>                                             | 7.62 mm                                                      |
| <b>Connection Type:</b>                                     | ADO System                                                   |
| <b>Function:</b>                                            | Female Plugs                                                 |
| <b>Rated Current (I<sub>n</sub>):</b>                       | Main Circuit 16 A                                            |
| <b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b> | for 1 s 180 A                                                |
| <b>Rated Voltage (U<sub>r</sub>):</b>                       | 500 V                                                        |
| <b>Pollution Degree:</b>                                    | 3                                                            |
| <b>Degree of Protection:</b>                                | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |

## Technical UL/CSA

|                                          |                    |
|------------------------------------------|--------------------|
| <b>Maximum Operating Voltage UL/CSA:</b> | Main Circuit 300 V |
| <b>Connecting Capacity UL/CSA:</b>       | Stranded 16 AWG    |

## Certificates and Declarations (Document Number)

|                                        |                 |
|----------------------------------------|-----------------|
| <b>cUL Certificate:</b>                | 1SND163004A0203 |
| <b>Declaration of Conformity - CE:</b> | 1SSD235020C1002 |

Classifications

|                             |                            |
|-----------------------------|----------------------------|
| Object Classification Code: | X                          |
| ETIM 4:                     | EC002638 - Cable connector |
| ETIM 5:                     | EC002638 - Cable connector |
| ETIM 6:                     | EC002638 - Cable connector |

Container Information

|                                 |               |
|---------------------------------|---------------|
| Package Level 1 Units:          | 50 piece      |
| Package Level 1 Width:          | 61 mm         |
| Package Level 1 Depth / Length: | 220 mm        |
| Package Level 1 Height:         | 47 mm         |
| Package Level 1 Gross Weight:   | 0.3 kg        |
| Package Level 1 EAN:            | 3472599285378 |
| Package Level 2 Units:          | 1000 piece    |
| Package Level 3 Units:          | 48000 piece   |
| Product Packing Type:           | Box           |

