

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Male Plugs

General Information

Extended Product Type:	L36520511000
Product ID:	1SSA365205R1100
EAN:	3472599053571
Catalog Description:	FIC M ADO 5P/5.08 FERME Male Plugs
Long Description:	ADO plugs allow connection of 2 wires of the same size and nature.

Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	9.7 g
----------------------------	-------

Technical

Rated Cross-Section:	1 mm ²
Spacing:	5.08 mm
Connection Type:	ADO System
Function:	Male Plugs
Rated Current (I_n):	Main Circuit 13.5 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 120 A
Rated Voltage (U_r):	500 V
Pollution Degree:	3

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity UL/CSA:	Stranded 16 AWG

Certificates and Declarations (Document Number)

cUL Certificate:	1SND163008A0200
Declaration of Conformity - CE:	1SSD235020C1002

Classifications

Object Classification Code:	X
ETIM 4:	EC002638 - Cable connector
ETIM 5:	EC002638 - Cable connector
ETIM 6:	EC002638 - Cable connector

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	101 mm
Package Level 1 Depth / Length:	220 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.485 kg
Package Level 1 EAN:	3472599053571
Package Level 2 Units:	500 piece
Package Level 3 Units:	24000 piece
Product Packing Type:	Box

