

# L36520611000



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Male Plugs

## General Information

|                               |  |
|-------------------------------|--|
| <b>Extended Product Type:</b> | L36520611000   |
| <b>Product ID:</b>            | 1SSA365206R1100  |
| <b>EAN:</b>                   | 3472599053656  |
| <b>Catalog Description:</b>   | FIC M ADO 6P/5.08 FERME Male Plugs                                 |
| <b>Long Description:</b>      | ADO plugs allow connection of 2 wires of the same size and nature. |

## Ordering

|                                |          |
|--------------------------------|----------|
| <b>Color:</b>                  | Grey     |
| <b>Minimum Order Quantity:</b> | 50 piece |
| <b>Customs Tariff Number:</b>  | 85369010 |

## Dimensions

|                            |      |
|----------------------------|------|
| <b>Product Net Weight:</b> | 10 g |
|----------------------------|------|

## Technical

|   |                     |
|---|---------------------|
| <b>Rated Cross-Section:</b>                                 | 1 mm <sup>2</sup>   |
| <b>Spacing:</b>   | 5.08 mm             |
| <b>Connection Type:</b>                                     | ADO System          |
| <b>Function:</b>  | Male Plugs          |
| <b>Rated Current (I<sub>n</sub>):</b>                       | Main Circuit 13.5 A |
| <b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b> | for 1 s 120 A       |
| <b>Rated Voltage (U<sub>r</sub>):</b>                       | 500 V               |
| <b>Pollution Degree:</b>                                    | 3                   |

## Technical UL/CSA

|  |                    |
|--|--------------------|
| <b>Maximum Operating Voltage UL/CSA:</b> | Main Circuit 300 V |
| <b>Connecting Capacity UL/CSA:</b>       | Stranded 16 AWG    |

## Certificates and Declarations (Document Number)

|  |                 |
|--|-----------------|
| <b>cUL Certificate:</b>                | 1SND163008A0200 |
| <b>Declaration of Conformity - CE:</b> | 1SSD235020C1002 |

## Classifications

|                                    |                            |
|------------------------------------|----------------------------|
| <b>Object Classification Code:</b> | X                          |
| <b>ETIM 4:</b>                     | EC002638 - Cable connector |
| <b>ETIM 5:</b>                     | EC002638 - Cable connector |
| <b>ETIM 6:</b>                     | EC002638 - Cable connector |

## Container Information

|  |               |
|--|---------------|
| <b>Package Level 1 Units:</b>          | 50 piece      |
| <b>Package Level 1 Width:</b>          | 101 mm        |
| <b>Package Level 1 Depth / Length:</b> | 220 mm        |
| <b>Package Level 1 Height:</b>         | 47 mm         |
| <b>Package Level 1 Gross Weight:</b>   | 0.5 kg        |
| <b>Package Level 1 EAN:</b>            | 3472599053656 |
| <b>Package Level 2 Units:</b>          | 500 piece     |
| <b>Package Level 3 Units:</b>          | 24000 piece   |
| <b>Product Packing Type:</b>           | Box           |

