

Quick Reference Guide

Green Pushbutton and Toggle Series Switches

The Green Series switch offering includes both pushbutton and toggle switches all rated to 6A/3A@125/250VAC and 4A@28VDC. The life expectancy depending on function (momentary or push on push off) and number of poles from 40,000 up to 80,000 cycles at full load this is accomplished due to silver slugs in the contact area. In addition to the silver slugs all contact surfaces are gold flashed this inhibits oxidation and also offers a very low initial contact resistance. The design also includes overmolded terminals which eliminate any voids which is possible with epoxy sealed terminals. The Green Series Toggle offer wide range of toggle bat options including a splash proof switch the MTE series and locking toggle MTL series. In the pushbuttons we offer our standard button style MPA plus a splash proof design MPE and our very robust actuator the MPG Mustang series.

FEATURES AND BENEFITS

- Wire lug, PC terminals, right angle and vertical right angle offered
- Customer selected actuator cap size and color on MPA series
- MTE series splash proof toggle actuator
- MPE series sealed to IP65
- Entire series with overmolded terminals
- Actuator guards, decorative hardware, and silicone boot seals available

PRODUCT APPLICATIONS

- Military/Aerospace
- Commercial
- Industrial
- Instrumentation
- Medical




Typical Bayfaynanaa Chayratayistica	
Typical Performance Characteristics	
Contact configuration	spdt, dpdt, 3pdt, 4pdt
Contact timing	break-before-make
Contact rating, max	6 A @ 125 VAC, 3 A @ 250 VAC
Electrical life (pushbutton only)	push on/push off: 30,000 cycles momentary: 20,000 cycles
Contact resistance, initial	10 mOhms max.
Insulation resistance	1,000 MOhms min.
Dielectric strength	1,500 Volts rms @ sea level
Actuator force	4 to 20 N (400 to 2000 gf)
Actuator travel	3.44 mm (pushbuttons) 24°-26° (toggles)
Environmental Specifications	
Operating temperature	-20°C to +80°C
Storage temperature	-40°C to +80°C
Solder heat resistance	wave solder capable to 265°C
Seal	MPE switches IP65 overmolded terminals MTE series splash proof toggle actuator 'O' ring
Material Specifications	
Contacts	copper alloy silver clad gold flash
Actuator	brass nickel plated
Terminals	copper alloy silver clad gold flash
Terminal seal	overmolded
Case	alkyd polyester (green) UL94-V-O
Frame	stainless steel
Support bracket (toggle only)	steel nickel plated
Spring (toggle only)	music wire
RoHS Directive 2002/95/EC	compliant





PUSHBUTTON SWITCHES PRODUCT KEY





Product key	Bushing	No. of poles	Function	Terminals	Material	Part Number
MPA106D	1/4-40 3.4mm actuator	single pole	push-on/push-off	wire lug	RoHS compliant	2-1437567-8
MPA106F	1/4-40 3.4mm actuator	single pole	momentary	wire lug	RoHS compliant	2-1437567-9
MPA106FPC	1/4-40 3.4mm actuator	single pole	momentary	pcb	RoHS compliant	3-1437567-0
MPA206N	1/4-40 3.4mm actuator	double pole	push-on/push-off	wire lug	RoHS compliant	3-1437567-1
MPA206NPC	1/4-40 3.4mm actuator	double pole	push-on/push-off	pcb	RoHS compliant	3-1437567-2
MPA206R	1/4-40 3.4mm actuator	double pole	momentary	wire lug	RoHS compliant	3-1437567-3
MPA206RPC	1/4-40 3.4mm actuator	double pole	momentary	pcb	RoHS compliant	3-1437567-4
MPA306D	1/4-40 3.4mm actuator	3 poles	push-on/push-off	wire lug	RoHS compliant	3-1437567-5
MPA306F	1/4-40 3.4mm actuator	3 poles	momentary	wire lug	RoHS compliant	3-1437567-6
MPA406N	1/4-40 3.4mm actuator	4 poles	push-on/push-off	wire lug	RoHS compliant	3-1437567-7
MPA406R	1/4-40 3.4mm actuator	4 poles	momentary	wire lug	RoHS compliant	3-1437567-8
MPE106D	1/4-40 3.4mm actuator with 'O' ring	single pole	push-on/push-off	wire lug	RoHS compliant	4-1437567-2
MPE106F	1/4-40 3.4mm actuator with 'O' ring	single pole	momentary	wire lug	RoHS compliant	4-1437567-3
MPE206N	1/4-40 3.4mm actuator with 'O' ring	double pole	push-on/push-off	wire lug	RoHS compliant	4-1437567-4
MPE206R	1/4-40 3.4mm actuator with 'O' ring	double pole	momentary	wire lug	RoHS compliant	4-1437567-5
MPE306F	1/4-40 3.4mm actuator with 'O' ring	3 poles	momentary	wire lug	RoHS compliant	4-1437567-6
MPE406N	1/4-40 3.4mm actuator with 'O' ring	4 poles	push-on/push-off	wire lug	RoHS compliant	4-1437567-7
MPE406R	1/4-40 3.4mm actuator with 'O' ring	4 poles	momentary	wire lug	RoHS compliant	4-1437567-8
MPG106D	15/32-32 large actuator	single pole	push-on/push-off	wire lug	RoHS compliant	4-1437567-9
MPG106F	15/32-32 large actuator	single pole	momentary	wire lug	RoHS compliant	5-1437567-0
MPG206N	15/32-32 large actuator	double pole	push-on/push-off	wire lug	RoHS compliant	5-1437567-1
MPG206NPC	15/32-32 large actuator	double pole	push-on/push-off	pcb	RoHS compliant	5-1437567-2
MPG206R	15/32-32 large actuator	double pole	momentary	wire lug	RoHS compliant	5-1437567-3
MPG206RPC	15/32-32 large actuator	double pole	momentary	pcb	RoHS compliant	5-1437567-4
MPG306D	15/32-32 large actuator	3 poles	push-on/push-off	wire lug	RoHS compliant	5-1437567-5
MPG306F	15/32-32 large actuator	3 poles	momentary	wire lug	RoHS compliant	5-1437567-6
MPG406N	15/32-32 large actuator	4 poles	push-on/push-off	wire lug	RoHS compliant	5-1437567-7
MPG406R	15/32-32 large actuator	4 poles	momentary	wire lug	RoHS compliant	5-1437567-8



PC

TOGGLE SWITCHES PRODUCT KEY

D ON-ON

Terminations

blank wire lug

ON-OFF-ON

G (ON)-OFF-(ON) **H** ON-OFF-(ON)

PC printed circuit board VRA

ON-(ON)

Typical Product Key ΜT 06 Ε Туре MT Green Series toggle switches, panel mount Toggle & Bushing .410 long round toggle, 1/4-40 bushing .410 long round toggle, 1/4-40 bushing, right angle & vertical right angle .600 long round toggle with plastic tip, 1/4-40 bushing **A8** .410 long round toggle, 1/4-40 bushing with 'O' ring seal .485 long flat toggle, 1/4-40 bushing .452 long large diameter round toggle, 15/32 bushing .685 long large diameter round toggle, 15/32 bushing locking toggle, 1/4-40 bushing .270 long round toggle, 1/4-40 bushing М M8 .270 long round toggle, 1/4-40 bushing, right angle & vertical right angle Number of poles single poledouble pole 3 pole 4 pole Rating **06** 6 Amp Function 1 & 3 pole 2 & 4 pole 1 & 2 pole functionality *

ON-ON

s

RΑ

ON-OFF-ON

ON-(ON) (ON)-OFF-(ON)

vertical right angle

ON-OFF-(ON)

right angle





Product key	Toggle	Bushing	Poles	Terminations	Material	Part Number
TA106D	.410 round		1		RoHS Compliant	1-1437558-0
ITA106DPC	.410 round	1/4-40 bushing		wire lug	•	
		1/4-40 bushing	1	pc board	RoHS Compliant	1-1437558-1
MTA106E	.410 round	1/4-40 bushing	1	wire lug	RoHS Compliant	1-1437558-2
MTA106EPC	.410 round	1/4-40 bushing	1	pc board	RoHS Compliant	1-1437558-3
MTA106F	.410 round	1/4-40 bushing	1	wire lug	RoHS Compliant	1-1437558-4
MTA106FPC	.410 round	1/4-40 bushing	1	pc board	RoHS Compliant	1-1437558-5
MTA106G	.410 round	1/4-40 bushing	1	wire lug	RoHS Compliant	1-1437558-6
MTA106GPC	.410 round	1/4-40 bushing	1	pc board	RoHS Compliant	1-1437558-7
MTA206N	.410 round	1/4-40 bushing	2	wire lug	RoHS Compliant	2-1437558-0
MTA206NPC	.410 round	1/4-40 bushing	2	pc board	RoHS Compliant	2-1437558-1
MTA206P	.410 round	1/4-40 bushing	2	wire lug	RoHS Compliant	2-1437558-2
MTA206PPC	.410 round	1/4-40 bushing	2	pc board	RoHS Compliant	2-1437558-5
MTA206R	.410 round	1/4-40 bushing	2	wire lug	RoHS Compliant	2-1437558-7
MTA206RPC	.410 round	1/4-40 bushing	2	pc board	RoHS Compliant	2-1437558-8
MTA206S	.410 round	1/4-40 bushing	2	wire lug	RoHS Compliant	2-1437558-9
MTA206SPC	.410 round	1/4-40 bushing	2	pc board	RoHS Compliant	3-1437558-1
MTA306D	.410 round	1/4-40 bushing	3	wire lug	RoHS Compliant	3-1437558-5
MTA306DPC	.410 round	1/4-40 bushing	3	pc board	RoHS Compliant	3-1437558-6
MTA306E	.410 round	1/4-40 bushing	3	wire lug	RoHS Compliant	3-1437558-7
MTA306EPC	.410 round	1/4-40 bushing	3	pc board	RoHS Compliant	3-1437558-8
MTA306F	.410 round	1/4-40 bushing	3	wire lug	RoHS Compliant	3-1437558-9
MTA306FPC	.410 round	1/4-40 bushing	3	pc board	RoHS Compliant	4-1437558-0
MTA406N	.410 round	1/4-40 bushing	4	wire lug	RoHS Compliant	4-1437558-3
MTA406NPC	.410 round	1/4-40 bushing	4	pc board	RoHS Compliant	4-1437558-4
MTA406P	.410 round	1/4-40 bushing	4	wire lug	RoHS Compliant	4-1437558-5
MTA406PPC	.410 round	1/4-40 bushing	4	pc board	RoHS Compliant	4-1437558-8

ON-ON-ON

(ON)-ON-(ON)

* 2 and 4 pole design, internally

connected for 1 and 2 pole functionality

ON-ON-(ON)

PΑ



Product key MTB106D MTB106E						
	Toggle	Bushing	Poles	Terminations	Material	Part Number
MTB106E	.600 round, w plastic tip	1/4-40 bushing	1	wire lug	RoHS Compliant	6-1437558-2
	.600 round, w plastic tip	1/4-40 bushing	1	wire lug	RoHS Compliant	6-1437558-3
MTB206N	.600 round, w plastic tip	1/4-40 bushing	2	wire lug	RoHS Compliant	6-1437558-4
MTB206P	.600 round, w plastic tip	1/4-40 bushing	2	wire lug	RoHS Compliant	6-1437558-5
MTB306D	.600 round, w plastic tip	1/4-40 bushing	3	wire lug	RoHS Compliant	6-1437558-6
MTB406N	.600 round, w plastic tip	1/4-40 bushing	4	wire lug	RoHS Compliant	6-1437558-7
MTE106D	.410 round	1/4-40, O-ring seal	1	wire lug	RoHS Compliant	6-1437558-8
MTE106E	.410 round	1/4-40, O-ring seal	1	wire lug	RoHS Compliant	6-1437558-9
MTE106F	.410 round	1/4-40, O-ring seal	1	wire lug	RoHS Compliant	7-1437558-0
MTE106G	.410 round	1/4-40, O-ring seal	1	wire lug	RoHS Compliant	7-1437558-1
MTE206N	.410 round	1/4-40, O-ring seal	2	wire lug	RoHS Compliant	7-1437558-2
MTE206P	.410 round	1/4-40, O-ring seal	2	wire lug	RoHS Compliant	7-1437558-3
MTE206R	.410 round	1/4-40, O-ring seal	2	wire lug	RoHS Compliant	7-1437558-5
MTE206S	.410 round	1/4-40, O-ring seal	2	wire lug	RoHS Compliant	7-1437558-6
MTE306D	.410 round	1/4-40, O-ring seal	3	wire lug	RoHS Compliant	7-1437558-8
MTE306E	.410 round	1/4-40, O-ring seal	3	wire lug	RoHS Compliant	7-1437558-9
MTE406N	.410 round	1/4-40, O-ring seal	4	wire lug	RoHS Compliant	8-1437558-0
MTE406P	.410 round	1/4-40, O-ring seal	4	wire lug	RoHS Compliant	8-1437558-1
MTF106D	.485 flat	1/4-40 bushing	1	wire lug	RoHS Compliant	8-1437558-3
MTF106E	.485 flat	1/4-40 bushing	1	wire lug	RoHS Compliant	8-1437558-4
MTF106F	.485 flat	1/4-40 bushing	1	wire lug	RoHS Compliant	8-1437558-5
MTF106G	.485 flat	1/4-40 bushing	1	wire lug	RoHS Compliant	8-1437558-6
MTF206S	.485 flat	1/4-40 bushing	2	wire lug	RoHS Compliant	9-1437558-6
MTF306D	.485 flat	1/4-40 bushing	3	wire lug	RoHS Compliant	1437559-6
MTF406N	.485 flat	1/4-40 bushing	4	wire lug	RoHS Compliant	1437559-8
MTG106D	.452 large diam. round	15/32 bushing	1	wire lug	RoHS Compliant	1-1437559-1
MTG106E	.452 large diam. round	15/32 bushing	1	wire lug	RoHS Compliant	1-1437559-2
MTG106E	.452 large diam. round		1	wire lug	RoHS Compliant	1-1437559-3
	-	15/32 bushing				
MTG106G	.452 large diam. round	15/32 bushing	1	wire lug	RoHS Compliant	1-1437559-4
MTG206N	.452 large diam. round	15/32 bushing	2	wire lug	RoHS Compliant	1-1437559-8
MTG206P	.452 large diam. round	15/32 bushing	2	wire lug	RoHS Compliant	2-1437559-0
MTG206R	.452 large diam. round	15/32 bushing	2	wire lug	RoHS Compliant	2-1437559-2
MTG206S	.452 large diam. round	15/32 bushing	2	wire lug	RoHS Compliant	2-1437559-3
MTG306D	.452 large diam. round	15/32 bushing	3	wire lug	RoHS Compliant	2-1437559-8
MTG306E	.452 large diam. round	15/32 bushing	3	wire lug	RoHS Compliant	2-1437559-9
MTG406N	.452 large diam. round	15/32 bushing	4	wire lug	RoHS Compliant	3-1437559-1
MTG406P	.452 large diam. round	15/32 bushing	4	wire lug	RoHS Compliant	3-1437559-2
MTL106D	locking	1/4-40 bushing	1	wire lug	RoHS Compliant	3-1437559-4
MTL106E	locking	1/4-40 bushing	1	wire lug	RoHS Compliant	3-1437559-5
MTL206N	locking	1/4-40 bushing	2	wire lug	RoHS Compliant	3-1437559-7
MTL206P	locking	1/4-40 bushing	2	wire lug	RoHS Compliant	3-1437559-9
MTL206S	locking	1/4-40 bushing	2	wire lug	RoHS Compliant	4-1437559-1
MTL306D	locking	1/4-40 bushing	3	wire lug	RoHS Compliant	4-1437559-2
MTL306E	locking	1/4-40 bushing	3	wire lug	RoHS Compliant	4-1437559-3
MTL406N	locking	1/4-40 bushing	4	wire lug	RoHS Compliant	4-1437559-4
MTM106DPC	.270 round	1/4-40 bushing	1	pc board	RoHS Compliant	4-1437559-6
MTM106EPC	.270 round	1/4-40 bushing	1	pc board	RoHS Compliant	4-1437559-7
MTM106FPC	.270 round	1/4-40 bushing	1	pc board	RoHS Compliant	4-1437559-8
MTM206NPC	.270 round	1/4-40 bushing	2	pc board	RoHS Compliant	4-1437559-9
MTM306DPC	.270 round	1/4-40 bushing	3	pc board	RoHS Compliant	5-1437559-3
MTM406NPC	.270 round	1/4-40 bushing	4	pc board	RoHS Compliant	5-1437559-4
MTL106D	locking	1/4-40 bushing	1	wire lug	RoHS Compliant	3-1437559-4
MTL106E	locking	1/4-40 bushing	1	wire lug	RoHS Compliant	3-1437559-5
MTL206N	locking	1/4-40 bushing	2	wire lug	RoHS Compliant	3-1437559-7
MTL206P	locking	1/4-40 bushing	2	wire lug	RoHS Compliant	3-1437559-9
MTL206S	locking	1/4-40 bushing	2	wire lug	RoHS Compliant	4-1437559-1
MTL306D	locking	1/4-40 bushing	3	wire lug	RoHS Compliant	4-1437559-2
	locking	1/4-40 bushing	3	wire lug	RoHS Compliant	4-1437559-3
		1/4-40 bushing	4		RoHS Compliant	4-1437559-3
MTL306E	locking		1	wire lug pc board	RoHS Compliant	4-1437559-4 4-1437559-6
MTL306E MTL406N	270 round			nc poard	Runo Compliant	4-143/559-6
MTL306E MTL406N MTM106DPC	.270 round	1/4-40 bushing		-		
MTL306E MTL406N MTM106DPC MTM106EPC	.270 round	1/4-40 bushing	1	pc board	RoHS Compliant	4-1437559-7
MTL406N MTM106DPC MTM106EPC MTM106FPC	.270 round .270 round	1/4-40 bushing 1/4-40 bushing	1 1	pc board pc board	RoHS Compliant RoHS Compliant	4-1437559-7 4-1437559-8
MTL306E MTL406N MTM106DPC MTM106EPC	.270 round	1/4-40 bushing	1	pc board	RoHS Compliant	4-1437559-7



How to Specify in a Switch

Electrical Considerations

Voltage of Applications:	Current	of Application:			
Circuitry Configuration: Number of Poles:		Number of T	hrows:		
Number of Operations anticipated:					
Agency Approvals or Listings Desired:					
Mechaniclal Considerations					
Type of Switch (Actuator Type): Toggle	Pushbutton	Rota	iry	Rocker	_ Other
Switch Function (On/Off/On):	On/Off:		Momentary	/:	
Termination: Thru-Hole (PC) Surface	e Mount	_ Wire Lug	Quick (Connect	_ Other
Sealing Contamination Requirements:					
Product Processing Considerations					
Anticipated Soldering Process: Hand	Wave	SMT	Other		

FOR MORE INFORMATION

TE Technical Support Center

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: +52 (0) 55-1106-0800 Mexico +54 (0) 11-4733-2200 Latin/S. America: Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 +33 (0) 1-3420-8686 France: Netherlands: +31 (0) 73-6246-999 +86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined www.te.com/leadfree

te.com

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved. 2-1773458-6 CIS JG 05/2012

TE Connectivity and the TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

