



Introducing WPM White Polyester Matte Finish Label

TE Connectivity's (TE) new high-durability, white polyester label with matte finish is a thermal transfer printable label with a permanent acrylic adhesive. Its excellent clarity, high initial tack, high shear and ultimate adhesion make this label the perfect choice for a variety of indoor low surface energy applications. Where glossy labels can be highly reflective, the matte label finish effectively reduces glare when adhered to polished lighting fixtures, electronic components, etc. The label supports applications such as bar coding, PCB and component labeling, as well as general purpose labeling applications that require a high-durability white label. Even when exposed to a variety of solvents and elevated temperatures of as much as 200°F (93°C), the WPM white polyester matte finish label resists cracking and splitting, maintaining both its print quality and initial appearance.

KEY FEATURES

- Excellent dimensional stability at elevated temperatures
- Excellent chemical resistance
- Various colors available
- Thermal transfer printable
- Ink receptive topcoat

APPLICATIONS

- Bar code labeling
- Electronic device and equipment labeling
- Lighting
- Racks and panels
- General purpose label application

ENVIRONMENTAL AND STORAGE PROPERTIES

- Service temperature: -54°C to +93°C (-65°F to +200°F)
- Minimum application temperature: +2°C (+35°F)
- Shelf life: 2 years when stored at 21°C (+70°F) at 50% RH

PRINT TECHNOLOGY

- Thermal transfer label
- Recommended printer: T300 series
- Recommended ribbon: 1330-0607-10

STANDARDS

- Compliant to EU RoHS Directive 2002/95/EC

PRODUCT SAMPLES

Samples are available upon request. Please call +1 800-430-7226.

TECHNICAL DATASHEET

The technical datasheet TTDS-234 is available on te.com

te.com/products/identification-labeling



PRODUCT OFFERING

Part number	Part Description	Packaging Quantity	# AC	Label Width		Label Height		Horizontal Repeat		Vertical Repeat		Web Width		SAP #
				mm	in	mm	in	mm	in	mm	in	mm	in	
5-1899668-6	WPM-064064-25-9	25000	12	6,4	0,250	6,4	0,250	6,4	0,250	9,5	0,375	82,2	3,24	CR3436-000
5-1899668-7	WPM-080080-10-9	10000	8	8,0	0,315	8,0	0,315	9,9	0,39	13,3	0,525	83,3	3,28	CR3437-000
5-1899668-8	WPM-089047-10-9	10000	5	8,9	0,350	4,7	0,185	11,4	0,45	7,9	0,313	60,6	2,386	CR3446-000
6-1899668-0	WPM-095095-10-9	10000	7	9,5	0,375	9,5	0,375	11,1	0,437	12,7	0,5	64,3	2,531	CR3447-000
6-1899668-1	WPM-114040-25-9	25000	6	11,4	0,450	4,0	0,158	11,4	0,45	7,1	0,282	74,6	2,936	CR3448-000
6-1899668-2	WPM-127032-10-9	10000	5	12,7	0,500	3,2	0,126	19,1	0,75	6,4	0,25	94,6	3,736	CR3449-000
6-1899668-3	WPM-127064-10-9	10000	6	12,7	0,500	6,4	0,252	15,2	0,6	9,5	0,375	95,3	3,75	CR3450-000
6-1899668-4	WPM-127111-10-9	10000	5	12,7	0,500	11,1	0,437	16,8	0,662	14,3	0,563	86	3,38	CR3451-000
6-1899668-5	WPM-127127-10-9	10000	5	12,7	0,500	12,7	0,500	15,9	0,625	15,9	0,625	82,6	3,25	CR3452-000
6-1899668-6	WPM-165051-25-9	25000	4	16,5	0,650	5,1	0,200	17,8	0,7	8,3	0,325	75,8	2,99	CR3453-000
6-1899668-7	WPM-171171-10-9	10000	5	17,1	0,674	17,1	0,674	19,7	0,774	20,3	0,8	101,8	4,006	CR3454-000
6-1899668-8	WPM-178095-10-9	10000	4	17,8	0,700	9,5	0,375	19,1	0,75	12,7	0,5	80,9	3,19	CR3455-000
7-1899668-0	WPM-191064-10-9	10000	4	19,1	0,750	6,4	0,250	21,6	0,85	9,5	0,375	89,9	3,54	CR3457-000
7-1899668-1	WPM-203127-10-9	10000	4	20,3	0,800	12,7	0,500	22,9	0,9	15,9	0,625	94,6	3,73	CR3458-000
7-1899668-2	WPM-229064-10-9	10000	3	22,9	0,900	6,4	0,250	28,6	1,125	9,5	0,375	86	3,39	CR3459-000
7-1899668-3	WPM-254064-10-9	10000	3	25,4	1,000	6,4	0,250	27,9	1,1	9,5	0,375	95,3	3,75	CR3460-000
7-1899668-4	WPM-254097-10-9	10000	3	25,4	1,000	9,7	0,380	27,9	1,1	12,7	0,5	87,4	3,44	CR3461-000
7-1899668-5	WPM-254254-10-9	10000	3	25,4	1,000	25,4	1,000	27,9	1,1	28,6	1,125	87,4	3,44	CR3463-000
7-1899668-6	WPM-318064-10-9	10000	1	31,8	1,250	6,4	0,250	N/A	N/A	9,5	0,375	37,9	1,49	CR3464-000
7-1899668-7	WPM-318097-10-9	10000	1	31,8	1,250	9,7	0,380	N/A	N/A	12,7	0,5	37,9	1,49	CR3465-000
7-1899668-8	WPM-381064-10-9	10000	1	38,1	1,500	6,4	0,250	N/A	N/A	9,5	0,375	44,5	1,75	CR3466-000
7-1899668-9	WPM-381127-5-9	5000	2	38,1	1,500	12,7	0,500	44,2	1,74	15,9	0,625	88,2	3,47	CR3467-000
8-1899668-0	WPM-381191-5-9	5000	2	38,1	1,500	19,1	0,750	43,2	1,7	22,2	0,875	87,6	3,45	CR3468-000
8-1899668-1	WPM-445102-5-9	5000	1	44,5	1,750	10,2	0,400	N/A	N/A	12,7	0,5	50,4	1,986	CR3469-000
8-1899668-2	WPM-478175-5-9	5000	1	47,8	1,880	17,5	0,690	N/A	N/A	24,4	0,962	66	2,6	CR3470-000
8-1899668-3	WPM-508064-10-9	10000	1	50,8	2,000	6,4	0,250	N/A	N/A	9,5	0,375	56,9	2,24	CR3471-000
8-1899668-4	WPM-508095-5-9	5000	1	50,8	2,000	9,5	0,375	N/A	N/A	12,7	0,5	57,2	2,25	CR3472-000
8-1899668-5	WPM-508127-5-9	5000	1	50,8	2,000	12,7	0,500	N/A	N/A	15,9	0,625	56,9	2,24	CR3473-000
8-1899668-6	WPM-508254-5-9	5000	1	50,8	2,000	25,4	1,000	N/A	N/A	28,6	1,125	57,2	2,25	CR3474-000
8-1899668-7	WPM-508318-2.5-9	2500	1	50,8	2,000	31,8	1,250	N/A	N/A	34,9	1,375	56,9	2,24	CR3475-000
8-1899668-8	WPM-523841-1.5-9	1500	1	52,3	2,060	84,1	3,310	N/A	N/A	88,9	3,5	58,2	2,29	CR3476-000
8-1899668-9	WPM-699191-5-9	5000	1	69,9	2,750	19,1	0,750	N/A	N/A	23,3	0,917	76,2	3	CR3477-000
9-1899668-0	WPM-699254-5-9	5000	1	69,9	2,750	25,4	1,000	N/A	N/A	28,6	1,125	76,2	3	CR3478-000
9-1899668-1	WPM-762127-1-9	1000	1	76,2	3,000	127,0	5,000	N/A	N/A	129,5	5,1	79,4	3,13	CR3479-000
9-1899668-2	WPM-762254-5-9	5000	1	76,2	3,000	25,4	1,000	N/A	N/A	28,6	1,125	82,3	3,24	CR3480-000
9-1899668-3	WPM-762508-2.5-9	2500	1	76,2	3,000	50,8	2,000	N/A	N/A	54	2,125	82,6	3,24	CR3481-000

PART NUMBERING SYSTEM



te.com/products/identification-labeling

