



intercontec
products

623 Receptacle angled rotatable

speedtec - ready

17-pin

insulation insert uncoded

housing code 1

flange mount / Flange 25x25

Anti-vibration o-ring

Technical Data

number of pins 17
temperature range -20 °C to 130 °C
protection type when connected IP 66/67
rotation range 330°

Electrical Data

rated current max. 7 A*
rated voltage 125 V (AC/DC)
rated insulation voltage (L-L) 2000 V

mating cycles 500

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3
over voltage category III
max. height for operation 2000 m

Material

housing zinc diecast / chromated
insulation insert PBT, UL 94 / V0
seals FKM

Contacts (not part of product contents)

Tools (not part of product contents)

A E D C 113 N N 00 00 1215 000
A G C 113 N 00 00 1215 000



Contact Arrangement
mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Deutschland
Tel.: +49 9962 2002-0
Fax: +49 9962 2002-70
E-Mail: intercontec@te.com
Web: www.intercontec.biz



Main Dimensions
Receptacle angled rotatable

*for max. wire cross-section
pay attention to the
cross-section of used contacts