## **3SAT - SERIES**

## **Contact Load Ratings:**

High level (relay case grounded): Resistive: 2 amperes at 28 V dc.

0.3 ampere at 115 V ac, 60 to 400 Hz.

Inductive: 0.75 ampere at 28 V dc, 200 millihenries

Lamp: 0.1 ampere at 28 V dc.

Low level: 10 to 50  $\mu A$  at 10 to 50 mV dc or peak ac

## **Contact Resistance:**

Before: 0.05 ohm

During: 10 percent of open circuit voltage maximum.

After: 0.1 ohm

Life: 100,000 operations Operate Time:15 ms Release Time:10 ms Contact Bounce: 2ms

Dielectric:	Sea level V rms (60 Hz)	Altitude V rms (60 Hz)
Between case, frame or enclosure, and all contacts both in the energized and deenergized positions:	1,000	350
Between case, frame or enclosure and coil:	500	All terminals
Between all contacts and coil:	1,000	to case
Between open contacts in the energized and deenergized positions:  Between contact poles:	nclosure, and all contacts both in gized positions:	

Insulation Resistance: 1,000 megohms minimum

Vibration: 10 to 2000Hz, 15G's

Shock: 100G's, 6 ms

Temperature: 65C to +125C

Weight: 1.1 ounces max

DC coil resistance	Nominal coil	Pick up current	Drop out current	Drop out current
(±10%) 25°C	Current (mA)	Max	Max	Min
(ohms)		(mA)	(mA)	(mA)
20	90.0	45.0	22.5	4.5
100	40.0	20.0	10.0	2.0
200	28.4	14.2	10.0	1.4
500	18.0	9.0	4.5	0.9
1,000	13.0	6.5	3.1	0.7
1,500	11.0	5.2	2.6	0.5
2,000	9.0	4.5	2.2	0.5
2,500	8.0	4.0	2.0	0.4
5,000	6.0	2.8	1.4	0.3
8,000	5.0	2.3	1.1	0.2
10,000	4.0	2.0	1.0	0.2

TITLE



DATA SHEET

DS

3SAT-SERIES

TE P.N. DWG NO. 3SAT-SERIES

CAGE CODE SCALE SHEET REV
- NONE 1 OF 3 A



APPROVED

MB

DATE

22SEP2020


**REVISIONS** 


DESCRIPTION

REV.

ECO

INITIAL DRAWN





## 3SAT QPL Relay PN Chart

	REVISIONS						
REV.	ECO	DESCRIPTION	DATE	APPROVED			
Α	-	INITIAL DRAWN	22SEP2020	MB			

Milspec	PartNumber	Mil Spec-	Mil Spec- Terminals	Mil Spec-Coil Resistance	Mil Spec- Coil
		Enclosure	Terminais	Resistance	Current
M5757/13-083	3SAT1300A2	flange A	solder hooks	20	90.0mA
M5757/13-084	3SAT1300A2	flange A	solder hooks	100	40.0mA
M5757/13-084	3SAT1301A2	flange A	solder hooks	500	18.0mA
M5757/13-085	3SAT1302A2		solder hooks	1000	13.0mA
	3SAT1303A2 3SAT1304A2	flange A	solder hooks	1500	
M5757/13-087		flange A			11.0mA
M5757/13-088	3SAT1305A2	flange A	solder hooks	2000	9.0mA
M5757/13-089	3SAT1306A2	flange A	solder hooks	2500	8.0mA
M5757/13-090	3SAT1307A2	flange A	solder hooks	5000	6.0mA
M5757/13-091	3SAT1308A2	flange A	solder hooks	8000	5.0mA
M5757/13-092	3SAT1309A2	flange A	solder hooks	10000	4.0mA
M5757/13-093	3SAT1310A2	flange A	pc pins	20	90.0mA
M5757/13-094	3SAT1311A2	flange A	pc pins	100	40.0mA
M5757/13-095	3SAT1312A2	flange A	pc pins	200	28.4mA
M5757/13-096	3SAT1313A2	flange A	pc pins	500	18.0mA
M5757/13-097	3SAT1314A2	flange A	pc pins	1000	13.0mA
M5757/13-098	3SAT1315A2	flange A	pc pins	1500	11.0mA
M5757/13-099	3SAT1316A2	flange A	pc pins	2000	9.0mA
M5757/13-100	3SAT1317A2	flange A	pc pins	2500	8.0mA
M5757/13-101	3SAT1318A2	flange A	pc pins	5000	6.0mA
M5757/13-102	3SAT1319A2	flange A	pc pins	8000	5.0mA
M5757/13-103	3SAT1320A2	flange A	pc pins	10000	4.0mA
M5757/13-104	3SAT1321A2	flange B	solder hooks	20	90.0mA
M5757/13-105	3SAT1322A2	flange B	solder hooks	100	40.0mA
M5757/13-106	3SAT1323A2	flange B	solder hooks	500	18.0mA
M5757/13-107	3SAT1324A2	flange B	solder hooks	1000	13.0mA
M5757/13-108	3SAT1325A2	flange B	solder hooks	1500	11.0mA
M5757/13-109	3SAT1326A2	flange B	solder hooks	2000	9.0mA
M5757/13-110	3SAT1327A2	flange B	solder hooks	2500	8.0mA
M5757/13-111	3SAT1328A2	flange B	solder hooks	5000	6.0mA
M5757/13-112	3SAT1329A2	flange B	solder hooks	8000	5.0mA
M5757/13-112	3SAT1329A2	flange B	solder hooks	10000	4.0mA
M5757/13-113	3SAT1330A2 3SAT1331A2	studs	solder hooks	20	90.0mA
	3SAT1331A2 3SAT1332A2	studs	solder hooks	100	40.0mA
M5757/13-115 M5757/13-116	3SAT1332A2 3SAT1333A2	studs	solder hooks	500	18.0mA
			solder hooks		
M5757/13-117	3SAT1334A2	studs		1000	13.0mA
M5757/13-118	3SAT1335A2	studs	solder hooks	1500	11.0mA
M5757/13-119	3SAT1336A2	studs	solder hooks	2000	9.0mA
M5757/13-120	3SAT1337A2	studs	solder hooks	2500	8.0mA
M5757/13-121	3SAT1338A2	studs	solder hooks	5000	6.0mA
M5757/13-122	3SAT1339A2	studs	solder hooks	8000	5.0mA
M5757/13-123	3SAT1340A2	studs	solder hooks	10000	4.0mA
M5757/13-124	3SAT1341A2	studs	wire leads	20	90.0mA
M5757/13-125	3SAT1342A2	studs	wire leads	100	40.0mA
M5757/13-126	3SAT1343A2	studs	wire leads	500	18.0mA
M5757/13-127	3SAT1344A2	studs	wire leads	1000	13.0mA
M5757/13-128	3SAT1345A2	studs	wire leads	1500	11.0mA
M5757/13-129	3SAT1346A2	studs	wire leads	2000	9.0mA
M5757/13-130	3SAT1347A2	studs	wire leads	2500	8.0mA
M5757/13-131	3SAT1348A2	studs	wire leads	5000	6.0mA
M5757/13-132	3SAT1349A2	studs	wire leads	8000	5.0mA
M5757/13-133	3SAT1350A2	studs	wire leads	10000	4.0mA
M5757/13-134	3SAT1351A2	bracket	solder hooks	20	90.0mA
M5757/13-135	3SAT1352A2	bracket	solder hooks	100	40.0mA
M5757/13-136	3SAT1353A2	bracket	solder hooks	500	18.0mA
M5757/13-137	3SAT1354A2	bracket	solder hooks	1000	13.0mA
M5757/13-138	3SAT1355A2	bracket	solder hooks	1500	11.0mA
M5757/13-139	3SAT1356A2	bracket	solder hooks	2000	9.0mA
M5757/13-140	3SAT1357A2	bracket	solder hooks	2500	8.0mA
M5757/13-141	3SAT1358A2	bracket	solder hooks	5000	6.0mA
M5757/13-142	3SAT1359A2	bracket	solder hooks	8000	5.0mA
M5757/13-143	3SAT1360A2	bracket	solder hooks	10000	4.0mA

<b>STE</b>
TE CONNECTIVITY
FAIRVIEW, NC

DATA SHEET

DS

TITLE	3SAT-SERIES			
TE P.N.		DWG NO.		
_		3SAT-S	SERIES	
CAGE CODE —	scale NON!		SHEET 3 OF 3	REV A