



TECHNICAL DATA SHEET

35-0010-B00-R

Battery Signal Switch

Technical Data

CASE MATERIAL	PA GF Black
SWITCH LEVER MATERIAL	PA GF Red
DIELECTRIC WITHSTAND VOLTAGE	700 VDC, 2 sec.
VOLTAGE	Up to 32 VDC
DUTY RATING	Max. 4 A
SEALING	IP 67 / IEC 529
VIBRATION	4G / 50-2000 Hz
SHOCK G-LEVEL	6G / 11 msec
WEIGHT	160 g
TEMPERATURE RANGE	-40°C to +85°C
MOUNTING POSITION	Optional
SWITCH LEVER	Removeable