



TECHNICAL DATA SHEET

35-0010-B30-R

Battery Signal Switch

Technical Data

| | |
|------------------------------|-----------------|
| CASE MATERIAL | PA GF Black |
| SWITCH LEVER MATERIAL | PA GF Red |
| DIELECTRIC WITHSTAND VOLTAGE | 700 VDC, 2 sec. |
| VOLTAGE | Up to 32 VDC |
| DUTY RATING | Max. 4 A |
| SEALING | IP 67 / IEC 529 |
| VIBRATION | 4G / 50-2000 Hz |
| SHOCK G-LEVEL | 6G / 11 msec |
| WEIGHT | 160 g |
| TEMPERATURE RANGE | -40°C to +85°C |
| MOUNTING POSITION | Optional |
| SWITCH LEVER | Removeable |