



FUSE CUTOUT COVER (BCAC-G-CUTOUT)

WILDLIFE AND ASSET PROTECTION PRODUCTS

KEY FEATURES

- Reliable outage protection
- Hot-stickable installation
- Rugged, non-tracking UV-resistant polymer

TE Connectivity's (TE) Raychem Fuse Cutout covers protect birds and animals from causing unwanted outages on polymer and porcelain style fuse cutouts.

The BCAC cover is a unique design that improves the level of protection by covering the back side of the cutout without effecting its operation. Three different cover styles are available and are designed to fit 100 and 200 AMP versions.

The single piece BCAC cover is quick and easy to install in the field. The cover is hot stick installable on energized fuse cutouts. The "saloon door" design allows easy installation onto the conductors while providing superior holding force.

Superior high-voltage outdoor materials are used in the BCAC cover design. The rugged, non tracking, UV-resistant polymer ensures long-term performance even in the most extreme environmental conditions.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Fuse Cutout Cover (BCAC-G-CUTOUT)

TE's wildlife and asset protection products and systems of tubes, tapes, sheets, pre-formed covers and barriers provide a proven, cost-effective and easy-to-install solution to bird, animal and weather related outages.



PRODUCT PERFORMANCE	
Description	Cutout Style
BCAC-G-CUTOUT-100-01-B12	100-AMP/Porcelain
BCAC-G-CUTOUT-200 (B3)	200-AMP/Porcelain
BCAC-G-CUTOUT-100-P2-B12	100-AMP/Polymeric (Hubbell & Cooper Style)



te.com/energy

©2011-2013, 2014 TE Connectivity Ltd. family of companies. All Rights Reserved. 9-1773462-3 E462 10/2014

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Benelux:	+ 32 16 351 731
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
China:	+ 86 (0) 400-820-6015