





MODEL EGAS ACCELEROMETER

SPECIFICATIONS

- Miniature Design, Light Weight
- **DC Response, Critically Damped** 4
- 4 10.000 g Over-range Stops
- **Broad Temperature Range**

The Model EGAS is a miniature, uniaxial accelerometer featuring ranges from ±5g through ±2500g. This rugged unit weighs less than 1 gram (without leads) and has an overrange limit of 10,000g's. The 1/2 active bridge is suitable for shunt calibration. With an operating temperature range of -40°C to +120°C, the EGAS is the unit of choice for measurement professionals in the automotive, military, aerospace and transportation industries. Its combined nonlinearity and hysteresis of ±1% makes the EGAS wellsuited for on-site testing as well as laboratory use.

- 2-15Vdc Excitation Voltage
- Weighs < 1 gram
- Static and Dynamic Measurement
- Frequency Response through 3500 Hz

ACCELEROMETER

MODULE

Red

Black

+ Input

Green + Output

White _ - Output

_ - Input

- 2% Transverse Sensitivity
- **Damping Ratio 0.7**

APPLICATIONS

- Sports and Recreation
- **Modeling and Entertainment**
- **Automotive Testing**
- Laboratory Usage

PERFORMANCE SPECIFICATIONS

All values are typical at +24°C, 100Hz and 15Vdc excitation unless otherwise stated. Measurement Specialties reserves the right to update and change these specifications without notice. Standard product parameters are described in PSC-1004 for Plug & Play DC Accelerometers.

Parameters										Netes
DYNAMIC Range (g)	±5	±10	±25	±50	±100	±250	±500	±1000	±2500	Notes
Sensitivity (mV/g) Frequency Response	20 0-80	10 0-120	4 0-240	2 0-350	1 0-500	0.4 0-750	0.2 0-	0.1 0-	0.04 0-	±1/2dB
min. (Hz)							1000	1500	2000	
Frequency Response nom. (Hz)	0-150	0-200	0-400	0-600	0-900	0-1300	0- 1750	0- 2500	0- 3500	±1/2dB
Natural Frequency (Hz) Non-Linearity (%FSO)	300 ±1	400 ±1	800 ±1	1200 ±1	1800 ±1	2600 ±1	3500 ±1	5000 ±1	7000 ±1	
Transverse Sensitivity	<u>-</u> 1 <2	<2	<2	<2	±1 <2	±1 <2	±1 <2	<2	<2	
(%) Damping Ratio	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	Nominal
Shock Limit (g)	500	1000	2000	5000	10000	10000	10000	10000	10000	
ELECTRICAL										
Zero Acceleration Output (mV)	±15 Differentia								Differentia I	
Excitation Voltage (Vdc)	15 (can be used from 2 to 15Vdc but lower excitation voltage will decrease sensitivity accordingly)									
Input Resistance (Ω) Output Resistance (Ω)	1300 Nominal 1500 Nominal									
Insulation Resistance (MΩ)	>100 @50Vdc									
Ground Isolation	Isolated from Mounting Surface									
ENVIRONMENTAL										
Thermal Zero Shift Thermal Sensitivity Shift	±1.0mV / 50°C (±1.0mV / 100°F) ±2.5% / 50°C (±2.5% / 100°F)									
Operating Temperature	-40 to +120°C (-40 to +250°F)									
Compensated Temperature	+20 to+80°C (+70 to +170°F), contact factory for other temperature compensation options									
Storage Temperature	-40 to +120°C (-40 to +250°F)									
Humidity	Epoxy S	Epoxy Sealed								
PHYSICAL Case Material	Stainles	e Stool								
Cable	Stainless Steel 4x #34 AWG Conductors PTFE Insulated, Shielded & Jacketed on –FS & -FT Options									
Weight Mounting	1 grams Screw Mount for EGAS-F, Adhesive Mount for EGAS									
-										
Wiring color code:	+Excitation = Red; -Excitation = Black; +Output = Green; -Output = White									
Calibration supplied:	CS-FRE	CS-FREQ-0100 NIST Traceable Amplitude Calibration from 20Hz to ±1/2dB Frequency Response Limit								
Optional accessories:		MTG-F2 Triaxial Mounting Block for EGAS-FS & -FT								
	MTG-F3 121	5	Triaxial Mounting Block for EGAS-F 3-Channel Precision Low Noise DC Amplifier							
	140				e Amplifier		•			

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.

ORDERING INFO

EGAS – F – 100 – /Z1/L2M/C	Compensated Temp Ranges:	Standar	rd = +20 to +80°C (+70 to +170°F)		
I I I Options, otherwi	se leave blank	Z1	= -20 to +40°C (0 to +100°F)		
I I Range (100 is 10	00g)	Z2	= 0 to +60°C (+32 to +140°F)		
I Housing (-F, -FS	, -FT or leave blank)	Z4	= +40 to +90°C (+100 to +200°F)		
0 ()	,	Z*	= Non standard, contact factory		
Excitation Voltage:		Standard = 15Vdc			
	C C	V*	= Non standard, contact factory		
	Special Cable Length:	LOOF	= Replace "00" with length in feet		
	1 5	LOOM	= Replace "00" with length in meter		
	Connector Wired to Cable:	С	= Microtech type male or equivalent		
		R	= RJ Telephone Male, for EGAS & -F		

Example: EGAS-F-100-/L2M

Model EGAS, F Housing Configuration, 100g Range, 2 Meter Cable Length

= RJ Telephone Male, for -FS & -FT

RS

NORTH AMERICA

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752 Email: <u>customercare.hmpt@te.com</u>

EUROPE

MEAS France SAS a TE Connectivity Company Tel: 800-440-5100 Email: <u>customercare.lcsb@te.com</u>

ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015 Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity enducts should make their own evaluation to determine the suitability of each such product for the specific application.

07/2017

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

