



## ELASTOMER CABLE BREAKOUTS CBO

### FLEXIBLE CABLE BREAKOUTS FOR MULTI-CORE POLYMERIC CABLES 0.6/1 kV

#### KEY FEATURES

- Reliable protection against humidity, dirt and mechanical damage
- For round and sector shaped conductors
- Black TPE material with high elasticity
- Easy to install, no tools needed
- Good tensile strength

TE Connectivity's (TE) cable breakouts are used as reliable termination of polymeric insulated cables in house connection boxes, lighting poles, switchgear and transformer stations.

They are made of thermoplastic elastomer (TPE) which is weather and UV-resistant. Due to the high elasticity, all cable breakouts fit round as well as sector shaped conductors.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



## PRODUCT SELECTION INFORMATION

Description	Number of Cores	Cross Section [mm <sup>2</sup> ]	Shape	Pack Size	Part Number
GURO-CBO-3X2,5	3	1,5 - 4	round	10	604866-000
GURO-CBO-3X6	3	6	round	10	054258-000
GURO-CBO-3X10	3	10	round	10	756860-000
GURO-CBO-3X16	3	16	round	10	547810-000
GURO-CBO-3X25	3	25	round	10	444342-000
GURO-CBO-4X2,5	4	1,5 - 2,5	round	10	319828-000
GURO-CBO-4X4	4	4	round	10	443812-000
GURO-CBO-4X6	4	6	round	10	793274-000
GURO-CBO-4X10	4	10	round	10	863316-000
GURO-CBO-4X16	4	16	round	10	476444-000
GURO-CBO-4X25	4	25	round	10	453786-000
GURO-CBO-4X35	4	35	round	10	436260-000
GURO-CBO-4X50	4	50	round	10	064292-000
GURO-CBO-4X70S	4	70	sector	10	435152-000
GURO-CBO-4X95S	4	95	sector	10	438214-000
GURO-CBO-4X120S	4	120	sector	10	983106-000
GURO-CBO-4X150S	4	150	sector	10	678778-000
GURO-CBO-4X185S	4	185	sector	10	341722-000
GURO-CBO-5X2,5	5	1,5 - 4	round	10	801084-000
GURO-CBO-5X6	5	6	round	10	889022-000
GURO-CBO-5X10	5	10	round	10	176134-000

[te.com/energy](http://te.com/energy)

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-1966-10/14

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

### FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Benelux:	+ 32 16 351 731
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
China:	+ 86 (0) 400-820-6015