

# **UNDERGROUND CABLE JOINT SYSTEM BV**

FOR POLYMERIC INSULATED LV CABLES UP TO 25 mm<sup>2</sup>

#### **KEY FEATURES**

- Impact resistant
- Transparent housing
- Snap-to close design with labyrinth sealing
- Integrated range taking foam sealings at cable entry
- Available with environmentfriendly and label-free resin GUROFLEX-N

TE Connectivity's (TE's) Underground Cable Joint System BV consists of an impact-resistant, transparent polycarbonate housing with labyrinth and polymer foams for sealing at the cable entries.

Its snap-to-close design makes for simple installation. The robust housing, is easy and quickly to assemble, cutting to the cable diameter is not needed.

The filler material is delivered in double chamber bags. The connector blocks allow a quick and easy connection with fixed connector distance. Application range covers the cable cross sections from 1,5 mm<sup>2</sup> up to 25 mm<sup>2</sup>.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



## **Underground Cable Joint System BV**








Joints are tested according to CENELEC EN 50393; Connectors according to EN 61238-1 (VDE 0220 T.2/10.77).

PRODUCT DIMENSIONS								
BV-0		BV-1	BV-2					
Α	45	50	61					
В	144	154	190					
С	184	194	230					
D	220	230	270					
E	60	60	80					
F	13 - 20	16 - 25	21 - 30					



PRODUCT SELECTION INFORMATION								
Description	Connectors	Filler type	Volume	Cable Cross Section min [mm²]	Cable Cross Section max [mm²]	Part Number		
BV-0-43BD	without	RAPID 4300B	0,35	4 - 5 x 1,5	4 - 5 × 6	965798-000		
BV-0-GD	without	GUROFLEX-N	0,35	4 - 5 x 1,5	4 - 5 × 6	532736-000		
BV-0-43BD-KS0	KS-0	RAPID 4300B	0,35	4 - 5 x 1,5	4 - 5 × 6	194412-000		
BV-0-GD-KS0	KS-0	GUROFLEX-N	0,35	4 - 5 x 1,5	4 - 5 × 6	E97284-000		
BV-1-43BD	without	RAPID 4300B	0,35	4 - 5 × 4	4 - 5 x 16	857232-000		
BV-1-GD	without	GUROFLEX-N	0,35	4 - 5 x 4	4 - 5 X 16	969494-000		
BV-1-43BD-KS1	KS-1	RAPID 4300B	0,35	4 - 5 × 4	4 - 5 X 16	842724-000		
BV-1-GD-KS1	KS-1	GUROFLEX-N	0,35	4 - 5 × 4	4 - 5 X 16	D07457-000		
BV-2-43BD	without	RAPID 4300B	0,55	4 X 16	4 X 25	701086-000		
BV-2-GD	without	GUROFLEX-N	0,55	4 X 16	4 X 25	125766-000		
BV-2-43BD-KS2	KS-2	RAPID 4300B	0,55 l	4 X 16	4 X 25	544958-000		
BV-2-GD-KS2	KS-2	GUROFLEX-N	0,55	4 X 16	4 X 25	D90416-000		







### te.com/energy

©2014 - 2016 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2331-DDS-5/16-EN-EMEA-BV-TE

TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any attisements to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

## FOR MORE INFORMATION: TE Technical Support Centers

USA: + 1800 327 6996 + 33 380 583 200 France: UK: + 44 0870 870 7500 Germany: + 49 896 089 903 Spain: + 34 916 630 400 + 39 333 250 0915 Italy: Benelux: + 32 16 351 731 +1 (905) 475-6222 Canada: Mexico: + 52 (0) 55-1106-0800 Latin/S. America: + 54 (0) 11-4733-2200 China: + 86 (0) 400-820-6015

