



FUSE BOX EKM-2042

FUSE BOX FOR APPLICATION IN LIGHTING POLES OR OUTDOOR

KEY FEATURES

- Suitable for application in lighting poles with diameter ≥ 70 mm
- Suitable for outdoor application, impact resistant, flame retardant housing
- Sliding terminals allow simple and secure connection up to 10 (16) mm²
- Touch proof at maintenance even with removed cover
- Prewired with brass bars
- Easy installation with push in luminaire cable rubber glands

TE Connectivity's (TE) EKM-2042 was developed to meet expectations with respect to ease of assembly and reliability. It is a cost effective solution to connect and protect luminaires in lighting poles.

With its sliding terminals EKM-2042 can be installed fast and reliably in all street lighting grids.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Fuse Box EKM-2042



Type tested according to VDE 0660-505 and DIN 43628.

TECHNICAL DATA	
Detail	Data
Application range	inside of lighting poles (SK) or outdoor (SKF)
Pole inner diameter	≥ 70 mm
Minimum dimension of hand hole W x H	66 x 240 mm
Degree of protection	IP 43 (SK) or IP 55 (SKF)
Protection class	II
Cable cross section feeder cable	up to 3 x 5 x 2,5 - 10 mm ² or 3 x 5 x 6 mm ² (cable dia. 3 x 16 - 23 mm)
Cable cross section luminaire cable	1/2 x 3 x 1,5 mm ² - 1/2 x 5 x 2,5 mm ² (cable dia. 8 - 13 mm)
Dimensions H x W x D	240 x 66 x 55 mm
Feeder cable terminals	5-pole with sliding terminals
Fuse system	2 X D01 plug type
Pinning	universal
Protection against contact to life parts	acc. BGV A3
Material	impact resistant, flame retardant, thermoplastic material
Cover details	cover with screw lock, wire sealable
Luminaire cable sealing	1 double rubber gland

PRODUCT SELECTION INFORMATION					
Description		for 1 cable (mm ²)	for 2 cables (mm ²)	for 3 cables (mm ²)	Part Number
EKM-2042SK-2D1-6	SK, with transparent cover, 2 fuseholder D01, 2 fuses 6 A, pinning L1, L2, <L3>, N, PE(N)	5 x 2,5 - 10	5 x 2,5 - 10	5 x 2,5 - 10	D35657-000
EKM-2042SK-2D1-6-E42	SK, with transparent cover, 2 fuseholder D01, 2 fuses 6 A, pinning L1, L2, <L3>, N, PE(N), earthing wire 6 mm ² , green/Yellow 400 mm with screw M8x12	5 x 2,5 - 10	5 x 2,5 - 10	5 x 2,5 - 10	D56795-000
EKM-2042SKF-2D1-6	SKF, IP55, with grey cover, 2 fuseholder D01, 2 fuses 6 A, pinning L1, L2, <L3>, N, PE(N)	5 x 2,5 - 10	5 x 2,5 - 10	5 x 2,5 - 10	A96972-000
EKM-2042SKF-2D1-6-E42	SKF, IP55, with grey cover, 2 fuseholder D01, 2 fuses 6A, pinning L1, L2, <L3>,N, PE(N), earthing wire 6 mm ² , green/Yellow 400 mm with screw M8x12	5 x 2,5 - 10	5 x 2,5 - 10	5 x 2,5 - 10	D96784-000
EKM-2042F-2D1-6-IP2X	SKF, IP55, with grey cover, 2 fuseholder D01, 2 fuses 6 A, pinning L1, L2, <L3>, N, PE(N), with partially insulated sliding terminals	5 x 2,5 - 16	5 x 2,5 - 10	5 x 2,5 - 10	CB7471-000

te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2349-10/14

TE Connectivity and TE connectivity (Logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Benelux:	+ 32 16 351 731
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
China:	+ 86 (0) 400-820-6015