

LOOP-IN TERMINALS (LIT)

WITH PLUG FUSE HOLDERS FOR APPLICATION IN LIGHTING POLES

KEY FEATURES

- For lighting poles with small diameter
- Degree of protection IP2X

TE Connectivity's (TE) offers many types of Loop-In Terminals. All metal parts are corrosion free.

The LITO is a bare brass neutral bar for connection of N- and $\!\!/$ or PE-conductors.

The LIT1 is an insulated brass connector block for up to three wires of one phase and with means to connect one plug-in fuseholder for D01 fuses $^{2-10}$ 6

The LIT-42, LIT-52 and LIT-43 are connector blocks with mantle terminals for up to 4 underground cables up to 10 mm² cross section. Openings in the transparent cover allow to apply up to three plug-in fuse holder for D01 fuses 2-10 A.

The LIT-D1-xx are plug-in fuse holder, that match with the mantle terminals of the terminal blocks and the contact area of LIT1.

All metal parts are corrosion protected.

LIT1 with plug-in fuse can be applied in poles with inner diameter >54 mm, LIT4x and 5x require a minimum inner pole diameter of 75 mm.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.









PRODUCT SELEC Description		For 1	For 2	For 3	For 4	For 5	Part Number
Description		cable (mm²)	cables (mm²)	cables (mm²)	cables (mm²)	cables (mm²)	Part Number
Loop-in terminal bl	ocks						
GURO-LIT1	Loop-in terminal block 1-pole	1 x 2,5 - 16	1 x 2,5 - 16	1 x 2,5 - 16	-	-	800874-000
GURO-LITO	Neutral terminal	1 x 2,5 - 16	1 x 2,5 - 16	1 x 2,5 - 16	1 x 2,5 - 16	1 x 2,5 - 16	704546-000
GURO-LIT42-0D1	Loop-in terminal block, 4-pole, Openings for up to two plug fuseholders	4 x 6 - 16	4 x 6 - 16	4 x 6 - 10	4 x 6 - 10	-	581212-000
GURO-LIT43-0D1	Loop-in terminal block, 4-pole, Openings for up to three plug fuseholders	4 × 6 - 16	4 × 6 - 16	4 × 6 - 10	4 × 6 - 10	-	780276-000
GURO-LIT52-0D1	Loop-in terminal block, 5-pole, Openings for up to two plug fuseholders	5 x 6 - 16	5 x 6 - 16	5 x 6 -10	-	-	936268-000
Plug-in fuse holders	s for loop-in terminal blocks						
GURO-LIT-D1-02	Plug-in fuse holder D01 (E14) with fuse cartridge 2A	1 x 1,5 - 2,5	-	-	-	-	263482-000
GURO-LIT-D1-04	Plug-in fuse holder D01 (E14) with fuse cartridge 4A	1 x 1,5 - 2,5	-	-	-	-	970958-000
GURO-LIT-D1-06	Plug-in fuse holder D01 (E14) with fuse cartridge 6A	1 x 1,5 - 2,5	-	-	-	-	449552-000
GURO-LIT-D1-10	Plug-in fuse holder D01 (E14) with fuse cartridge 10A	1 x 1,5 - 2,5	-	-	-	-	659268-000
Loop-in terminal bl	ocks with plug-in fuseholders	5					
GURO-LIT42-1D1-6	Loop-in terminal block, 4-pole, with one plug fuseholder D01, 6A and second openingfor additional fuse holder (closed with plastic plug)	4 x 6 - 16	4 x 6 - 16	4 x 6 - 10	4 x 6 - 10	-	749748-000
GURO-LIT52-1D1-6	Loop-in terminal block, 5-pole, with one plug fuseholder D01, 6A and second openingfor additional fuse holder (closed with plastic plug)	5 x 6 - 16	5 x 6 - 16	5 x 6 - 10	-	-	738100-000

te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2375-10/14

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

+ 1 800 327 6996 USA: + 33 380 583 200 + 44 0870 870 7500 France: UK: + 49 896 089 903 Germany: Spain: + 34 916 630 400 Benelux: + 32 16 351 731 Canada: +1 (905) 475-6222 + 52 (0) 55-1106-0800 + 54 (0) 11-4733-2200 + 86 (0) 400-820-6015 Mexico: Latin/S. America: China:

