

# **FUSE BOX EKM-2035**

# FUSE BOX FOR APPLICATION IN LIGHTING POLES

#### **KEY FEATURES**

- Suitable for application in lighting poles with diameter ≥ 110 mm
- Sliding terminals allow simple and secure connection up to 50 mm<sup>2</sup>
- Touch proof at maintenance
- Version with DIN-rail can be equipped with MCBs or other installation devices; cover cut-out can be easily adapted

TE Connectivity's (TE) EKM-2035 provides a proven solution for connection and protection of luminaires in lighting poles. With its installer-friendly sliding terminals, EKM-2035 can be mounted fast and reliably in all 4-pole street lighting grids.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.









| TESTING                                  |  |  |  |  |
|--|--|--|--|--|
| Detail                                   | Data   |  |  |  |
| Application range                        | inside of lighting poles   |  |  |  |
| Pole inner diameter                      | > 110 mm   |  |  |  |
| Min. dimension of hand hole W x H        | 90 x 300 mm  |  |  |  |
| Degree of protection                     | IP 44  |  |  |  |
| Protection class                         |  |  |  |  |
| Cable cross section feeder cable         | up to 2 x 4 x 4 - 50 mm <sup>2</sup> or 3 x 4 x 4 - 35 mm <sup>2</sup> (cable dia. 16 - 35 mm)                 |  |  |  |
| Cable cross section luminaire cable      | 1 x 3 x 1,5 mm <sup>2</sup> - 2 x 5 x 2,5 mm <sup>2</sup> ( cable dia. 8-14 mm) or 2 x 4 wires dia. 1,5 - 3 mm |  |  |  |
| Dimensions H x W x D                     | 290 x 93,5 x 89 mm   |  |  |  |
| Feeder cable terminals                   | 4 sliding terminals  |  |  |  |
| Fuse system                              | 1/ 2 X D II (E27)  |  |  |  |
| Pinning                                  | L1, L2, L3, PEN  |  |  |  |
| Protection against contact to life parts | acc. BGV A3  |  |  |  |
| Material                                 | impact resistant, flame retardant, thermoplastic material  |  |  |  |
| Cover details                            | transparent cover with screw lock for fuse maintenance   |  |  |  |
| Luminaire cable sealing                  | 2 rubber glands  |  |  |  |

| PRODUCT SELECTION INFORMATION |   |                      |                       |                       |                |  |
|-------------------------------|---|----------------------|-----------------------|-----------------------|----------------|--|
| Description                   |   | for 1 cable<br>(mm²) | for 2 cables<br>(mm²) | for 3 cables<br>(mm²) | Part<br>Number |  |
| EKM-2035-1D2                  | 1 fuseholder DII (E27),<br>4 sliding terminals  | 4 x 4-50             | 4 x 4-50              | 4 x 4-35              | 059062-000     |  |
| EKM-2035-2D2                  | 2 fuseholder2 DII (E27),<br>4 sliding terminals | 4 x 4-50             | 4 x 4-50              | 4 x 4-35              | A27844-000     |  |
| EKM-2035-1R                   | 1DIN-rail, 4 sliding terminals                  | 4 × 4-50             | 4 x 4-50              | 4 × 4-35              | E67365-000     |  |
| EKM-2035-0D0                  | 4 sliding terminals                             | 4 x 4-50             | 4 x 4-50              | 4 x 4-35              | E84793-000     |  |

## te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2378-10/14

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

### FOR MORE INFORMATION: TE Technical Support Centers

+ 1 800 327 6996 USA: + 33 380 583 200 + 44 0870 870 7500 France: UK: + 49 896 089 903 Germany: Spain: + 34 916 630 400 Benelux: + 32 16 351 731 Canada: +1 (905) 475-6222 + 52 (0) 55-1106-0800 + 54 (0) 11-4733-2200 + 86 (0) 400-820-6015 Mexico: Latin/S. America: China:

