

EMPTY STREET LIGHTING BOXES PROTECTION FOR INSIDE OF LIGHTING POLES

KEY FEATURES

- Suitable for application in lighting poles
- With fixing means for different devices

TE Connectivity's (TE) empty housings are used to protect different types of custom devices when mounted inside of lighting poles.

Several different rails and covers are available to suit the customers individual needs for the EKM-2050 series.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.







PRODUCT SELECTION INFORMATION				
Description			Part Number	
EKM-1282-EM-2PG16-C2	Pole dia > 120 mm, IP 54,2 compression glands Pg 16	1 - 2 cables < Ø 30 mm	112954-000	
EKM-2045-EM-G	Pole dia > 59 mm, IP 54,1 rubber gland	1 - 2 cables < Ø 17 mm	CN6953-000	
EKM-2050-EM	Pole dia > 89 mm, IP 54,1 2 rubber glands	1-3 cables < Ø 24 mm	353276-000	
EKM-2050-1R/A	Pole dia > 102 mm, IP 54,1 2 rubber glands, transparent cover, 1 DIN-rail for installation devices 3 TE wide	1-3 cables < Ø 24 mm	E32027-000	
EKM-2055-1R/S	Pole dia > 100 mm, IP 54,1 2 rubber glands, transparent cover, 1 DIN-rail for installation devices 3 TE wide	1-3 cables < Ø 24 mm	CM5729-000	
EKM-2055F-1R/S	Pole dia > 100 mm, IP 54,1 2 rubber glands, gray cover, 1 DIN-rail for installation devices 3 TE wide	1-3 cables < Ø 24 mm	CM5728-000	
Modular housing system for EKM-2	050 and EKM-2051			
GURO-SET-CASE-2050	Base, cable clamp, rubber glands of EKM-2050 (covers to be ordered separately)		CE3869-000	
GURO-SET-CASE-2051	Base, cable clamp, rubber glands of EKM-2050 (covers to be ordered separately)		CE3870-000	
GURO-RAIL/A-EKM-205X	DIN-rail type A adaptable to EKM-2050 and EKM-2051		CE3865-000	
GURO-RAIL/B-EKM-205X	DIN-rail type B adaptable to EKM-2050 and EKM-2052		CE3866-000	
GURO-RAIL/C-EKM-205X	DIN-rail type C adaptable to EKM-2050 and EKM-2053		CE3867-000	
GURO-RAIL/D-EKM-205X	DIN-rail type D adaptable to EKM-2050 and EKM-2054		CE3868-000	
GURO-TB-5S-EKM2050-51	Terminal block with 5 sliding terminals		EE4607-000	
GURO-SET-CG-MG-EKM-205X	Set with 1 compression gland and one membrane gland for EKM-205x		584116-000	
GURO-SET-SKF-EKM2050	Set to build EKM-2050 from transparent cover (flat) with latch to gray cover with latch and screw lock		167224-000	
GURO-SET-SKF-EKM2051-F	Set to build EKM-2051 from transparent cover (flat) with latch to gray cover with latch and screw lock		413472-000	
GURO-SET-SKFH-EKM2050	Set to build EKM-2050 from transparent cover (flat) with latch to gray cover with latch and screw lock plus compression gland		326262-000	
GURO-SET-SKFH-EKM2051-F	Set to build EKM-2051 from transparent cover (flat) with latch to gray cover with latch and screw lock plus compression gland		934912-000	
GURO-SET-SKFH-EKM2051-H	Set to build EKM-2051 from transparent, high cover with latch to gray, high cover screw lock plus compression gland		C65466-000	
GURO-CO-2050-SKF/H	high gray cover for EKM 2050, with screw		CE3857-000	
GURO-CO-2051-SKF/H	high gray cover for EKM 2051, with screw		CE3855-000	

te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2379-11/14

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+1800 327 6996
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Benelux:	+ 32 16 351 731
Canada:	+1(905)475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
China:	+ 86 (0) 400-820-6015

