

WRAPTER FULL TENSION DEAD ENDS ALUMINIUM

KEY FEATURES

- Uniform grip to stop any distortion of the conductor or damage to the conductor
- Type Tested to AS 1154 at an Independent NATA certified Mechanical laboratory
- Colour coding to the requirements of AS 1154.3
- Easy Installation by hand or live line methods, no need for any special tools

TE Connectivity's (TE) are a leader in the design and supply of Helical Fittings for use on Utility and Distribution Networks across the ANZ region.

TE Connectivity can provide a wide range of WrapTEr helical terminations, joints, protection, restoration, repair and support fittings for use on bare and insulated overhead conductor. Each fitting is custom designed for a particular conductor range and type.

All fittings are manufactured from premium materials, which are compatible with the materials used in the conductor / cable onto which they are applied. This ensures maximum electrical and mechanical performance, whilst minimising corrosion potential.

Aluminium based dead-ends are designed to carry out terminations on overhead distribution networks for AAC, AAAC and ACSR style conductors. Their single, one piece design provides a uniform clamping load over a large cross section of the conductor.


A wide range of fittings have been developed to cover all conductors sizes/styles, with each specific application range as per the below table.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Wrapper Full Tension Dead Ends



On AAC and AAAC style conductors, WrapTER FAD fittings hold a minimum of 90% of the ultimate tensile strength of the conductor, onto which they are applied. For strength ratings on ACSR conductors, please consult TE.



ALUMINIUM FULL TENSION DEAD-ENDS ORDERING INFORMATION

TE Part Number	No. of Rods	Conductor Stranding	Conductor OD Range	Pack Quantity	Colour Code
FAD0515-0540-6	4	7/1.75	5.15 - 5.40	50	Purple
FAD0655-0710-6	4	7/2.25	6.55 - 7.10	50	Brown
FAD0735-0760-6	4	7/2.50	7.35 - 7.60	50	Blue
FAD0795-0860-6	4	7/2.75	7.95 - 8.60	40	White
FAD0865-0935-6	4	7/3.00	8.65 - 9.35	40	Red
FAD1015-1050-6	4	7/3.40	10.15 - 10.50	40	Blue
FAD1080-1130-6	4	7/3.75	10.80 - 11.30	25	Black
FAD1305-1405-6	6	7/4.50	13.05 - 14.05	20	Green
FAD1385-1445-6	6	7/4.75	13.85 - 14.45	20	Blue
FAD1565-1690-7	5	19/3.25	15.65 - 16.90	15	Orange
FAD1705-1780-7	5	19/3.50	17.05 - 17.80	10	Blue
FAD1855-1935-8	6	19/3.75	18.55 - 19.35	10	Black
FAD2020-2185-8	6	37/3.00	20.20 - 21.85	10	Red
FAD2245-2420-8	7	37/3.25	22.45 - 24.20	10	Blue
FAD2375-2620-8	6	19/4.75	23.75 - 26.20	10	Blue
FAD2530-2730-8	8	37/3.75	25.30 - 27.30	10	Black
FAD2860-3085-8	8	61/3.25	28.60 - 30.85	10	Orange

Unless specified otherwise, WrapTER fittings are of right-hand lay. Please specify on the order if items are required for left-hand lay.

te.com/energy

© 2019 TE Connectivity. All Rights Reserved. EPP-3346-DDS-4/19-FAD-TE-CONNECTIVITY

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+ 7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015