



WSMB MINIBOX

KEY FEATURES

- Thin wall heat shrink tubing in miniboxes
- Operating temperature: 40°C to 125°C
- 2:1 shrink ratio

TE Connectivity's (TE) WSMB Minibox offers a convenient packaging and dispensing option for a range of thin wall heat shrink tubing. The tubing is supplied on small reels which are overboxed and feature a dispensing window allowing the tube to be easily and readily accessed.

A varied selection of general purpose thin wall tubing is offered which will cover a diverse range of applications including electrical insulation, strain relief and cable bundling.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



PRODUCT SPECIFICATION

Type	Inner Diameter (mm)		Wall Thickness After Recovery (mm)	Length (m)
	As Supplied	After Recovery		
Black Color				
WSMB-16-1,6/0,8/S	1,6	0,8	0,45	20
WSMB-24-2,4/1,2/S	2,4	1,2	0,50	20
WSMB-32-3,2/1,6/S	3,2	1,6	0,50	20
WSMB-48-4,8/2,4/S	4,8	2,4	0,50	10
WSMB-64-6,4/3,2/S	6,4	3,2	0,65	10
WSMB-95-9,5/4,8/S	9,5	4,8	0,65	10
WSMB-127-12,7/6,4/S	12,7	6,4	0,65	10
WSMB-160-16,0/8,0/S	16,0	8,0	0,65	5
WSMB-190-19,0/9,5/S	19,0	9,5	0,75	5
WSMB-254-25,4/12,7/S	25,4	12,7	0,90	5
Red Color				
WSMB-16-1,6/0,8/R	1,6	0,8	0,45	20
WSMB-24-2,4/1,2/R	2,4	1,2	0,50	20
WSMB-32-3,2/1,6/R	3,2	1,6	0,50	20
WSMB-48-4,8/2,4/R	4,8	2,4	0,50	10
WSMB-64-6,4/3,2/R	6,4	3,2	0,65	10
WSMB-95-9,5/4,8/R	9,5	4,8	0,65	10
WSMB-127-12,7/6,4/R	12,7	6,4	0,65	10
WSMB-160-16,0/8,0/R	16,0	8,0	0,65	5
WSMB-190-19,0/9,5/R	19,0	9,5	0,75	5
WSMB-254-25,4/12,7/R	25,4	12,7	0,90	5
Blue Color				
WSMB-16-1,6/0,8/B	1,6	0,8	0,45	20
WSMB-24-2,4/1,2/B	2,4	1,2	0,50	20
WSMB-32-3,2/1,6/B	3,2	1,6	0,50	20
WSMB-48-4,8/2,4/B	4,8	2,4	0,50	10
WSMB-64-6,4/3,2/B	6,4	3,2	0,65	10
WSMB-95-9,5/4,8/B	9,5	4,8	0,65	10
WSMB-127-12,7/6,4/B	12,7	6,4	0,65	10
WSMB-160-16,0/8,0/B	16,0	8,0	0,65	5
WSMB-190-19,0/9,5/B	19,0	9,5	0,75	5
WSMB-254-25,4/12,7/B	25,4	12,7	0,90	5

Type	Inner Diameter (mm)		Wall Thickness After Recovery (mm)	Length (m)
	As Supplied	After Recovery		
Green/Yellow Color				
WSMB-32-3,2/1,6/G	3,2	1,6	0,50	20
WSMB-48-4,8/2,4/G	4,8	2,4	0,50	10
WSMB-64-6,4/3,2/G	6,4	3,2	0,65	10
WSMB-95-9,5/4,8/G	9,5	4,8	0,65	10
WSMB-127-12,7/6,4/G	12,7	6,4	0,65	10
WSMB-190-19,0/9,5/G	19,0	9,5	0,75	5
WSMB-254-25,4/12,7/G	25,4	12,7	0,90	5
Black Color				
WSMB-30-3,0/1,0/S	3,0	1,0	0,55	15
WSMB-60-6,0/2,0/S	6,0	2,0	0,65	10
WSMB-90-9,0/3,0/S	9,0	3,0	0,75	10
WSMB-120-12,0/4,0/S	12,0	4,0	0,75	8
WSMB-180-18,0/6,0/S	18,0	6,0	0,85	7
WSMB-240-24,0/8,0/S	24,0	8,0	1,00	4
Red Color				
WSMB-30-3,0/1,0/R	3,0	1,0	0,55	15
WSMB-60-6,0/2,0/R	6,0	2,0	0,65	10
WSMB-90-9,0/3,0/R	9,0	3,0	0,75	10
WSMB-120-12,0/4,0/R	12,0	4,0	0,75	8
WSMB-180-18,0/6,0/R	18,0	6,0	0,85	7
WSMB-240-24,0/8,0/R	24,0	8,0	1,00	4
Blue Color				
WSMB-30-3,0/1,0/B	3,0	1,0	0,55	15
WSMB-60-6,0/2,0/B	6,0	2,0	0,65	10
WSMB-90-9,0/3,0/B	9,0	3,0	0,75	10
WSMB-120-12,0/4,0/B	12,0	4,0	0,75	8
WSMB-180-18,0/6,0/B	18,0	6,0	0,85	7
WSMB-240-24,0/8,0/B	24,0	8,0	1,00	4

te.com/energy

© 2020 TE Connectivity. All Rights Reserved. EPP-3588-08/20

TE Connectivity, TE connectivity (logo), EVERY CONNECTION COUNTS, AMP, AMPACT, Axicom, Bowthorpe EMP, Crompton Instruments, Raychem, SIMEL, UTILUX are trademarks. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

**FOR MORE INFORMATION:
TE Technical Support Centers**

USA/Canada:	+1 800-327-6996
Brazil:	+55 11-2103-6023
Mexico:	+52 55-1106-0800
South America:	+57 1-319-8962
Benelux:	+32 16-508-695
France:	+33 (0) 38-058-3210
Germany/Switzerland:	+49 (0) 89-608-9903
Italy:	+39 335-834-3453
Middle East/Africa:	+971 4-211-7020
Russia:	+7 495-790-790-2-200
Spain/Portugal:	+34 912-681-885
UK:	+44 08708-707-500
China:	+86 400-820-6015