

COIL: @ +25°C

RESISTANCE 1030 Ω ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 11.4 VDC

MUST RELEASE 1.1 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 2500 CPS AT 20 g's

SHOCK 50 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES:

CUSTOMER DATA SHEET



CONTACT RATING: 2A @ 28 VDC
Resistive 100,000 operations

DR 8-12-91

CK. JmB



**Communications
Instruments, Inc.**

CUST. M39016/44-035L

CUST. NO. QPL

TYPE **HFW RELAY**

HMS 1201 S III L