


REV. 0  
DCO 143236

COIL: @ 25°C	
RESISTANCE	125 OHMS ±10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	2.8 VDC
MUST RELEASE	1.7 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 4.0 MS MAX.
	RELEASE TIME 7.5 MS MAX.
	CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	LOW LEVEL TO 1A
	28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 9/27/01

*K. Stepp* 9/27/01

**CII Technologies**  
advanced control electronic solutions

CUST. QPL  
CUST. NO. M39016/25-017M REV.

"JIMSD" RELAY

JIMSWD-5XM