


REV. 0
DCO 141815

COIL: @ 25°C	
RESISTANCE	1560 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	15.2 VDC
MUST RELEASE	9.5 VDC MAX, 1.8 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE TIME 2.0 MS MAX
	RELEASE TIME 4.0 MS MAX
	CONTACT STABILIZATION 2.0 MS MAX


CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. B.D. 2/28/00 *JKL* 2/28/00



JMACDD-26XPS2

JMADD RELAY

CUST. QPL
CUST. NO. M39016/20-078P REV. _____