


REV. 0  
DCO# 143125

COIL: @ 25°C	
RESISTANCE	98 OHMS ± 10%
NOMINAL VOLTAGE	6.0 VDC
MUST OPERATE	3.5 VDC
MUST RELEASE	2.0 VDC MAX, 0.28 VDC MIN

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES:	OPERATE TIME 2.0 MS MAX.
	RELEASE TIME 1.5 MS MAX.
	CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING:	LOW LEVEL TO 1A
	28 VDC RESISTIVE 100,000 OPERATIONS

DR. BSH 07/26/01 *[Signature]* 7/26/01



CUST. QPL  
CUST. NO. M39016/9-014L REV. \_\_\_\_\_

"JMA" RELAY

JMAW-6XL