



APPLICATIONS

- Abrasion protection for laparoscopic and in-vivo instruments
- High performance insulation for electrosurgical devices
- Strain relief applications

MT1000 PVDF HEAT SHRINK TUBING

PROFILE

- Shrink ratio ≤ 2:1
- Full recovery at 175°C (347°F) minimum
- Supports sterilization environments: gamma, ethylene oxide (ETO), steam, dry heat and autoclave
- Custom sizing, colors, finishing and value-add options available
- Radiopacity can be customized

ABOUT

- MT1000 is a crosslinked polyvinylidene fluoride (PVDF) heat shrink tubing. PVDF
 offers excellent chemical and abrasion resistance, high dielectric strength and
 superior tensile strength. Its homogeneous structure (properties evenly distributed)
 contributes to its consistency and high performance, making our MT1000 tubing
 essentially free from flaws, defects, pinholes, seams, cracks or inclusions
- MT1000 is rigid and highly-lubricious, and works very well at providing abrasion protection for rigid laparoscopic and in-vivo instruments

TABLE 1: DIMENSIONS

Chandend Circo	As Supplied Inside Diameter Minimum (D)		Recovered							
Standard Sizes			Inside Diameter Maximum (d)		Wall Thickness (in., mm.) (W)					
Size	in.	mm.	in.	mm.	Minimum		Maximum		Normal	
3/64	0.046	1.17	0.023	0.58	.008	0.20	0.012	0.31	.010	0.25
1/16	0.063	1.60	0.031	0.79	.008	0.20	0.012	0.31	.010	0.25
3/32	0.093	2.36	0.046	1.17	.009	0.20	0.012	0.31	.010	0.25
1/8	0.125	3.18	0.062	1.58	.009	0.20	0.012	0.31	.010	0.25
3/16	0.187	4.75	0.093	2.36	.009	0.20	0.012	0.31	.010	0.25
1/4	0.250	6.35	0.125	3.18	.011	0.28	0.015	0.38	.013	0.33
3/8	0.375	9.53	0.187	4.75	.011	0.28	0.015	0.38	.013	0.33
1/2	0.500	12.70	0.250	6.35	.011	0.28	0.015	0.38	.013	0.33

TABLE 2: PROPERTIES

Property	Unit	Requirement	Test Method		
Physical					
Dimensions*	inches (mm)	In accordance with Table 1			
Longitudinal change*	percent	+0, -10 maximum	ASTM D 2671		
Concentricity as supplied*	percent	70 minimum	ASTM D 2671		
Tensile strength*	psi (MPa)	5000 minimum (34.5)	ACTM D 2071 20" (minute		
Ultimate elongation*	percent	150 minimum	ASTM D 2671, 20"/minute		
Secant modulus* (expanded)	psi (MPa)	1 x 105 minimum (690)	ASTM D 2671		
Heat resistance 168 hours at 250 ± 5°C (482°F) Followed by test for: Ultimate elongation	percent	50 minimum	ASTM D 2671, 20"/minute		
Electrical					
Dielectric strength: Sizes 3/64 through 1/2	volts/mil	800 minimum (31.500)	ASTM D 2671		
Dielectric strength: Sizes 3/4 through 2	kV/mm	600 minimum (23.600)			
Dielectric withstand 3000V, 60Hz	sec	60 minimum	ASTM D 2671		
Chemical					
uid resistance 4 hours at 23 ± 3°C (73 ± 5°F) Isopropyl alcohol % saline solution Disinfectant					
Followed by tests for: Dielectric strength	1.57/	700 minimum (27.600)	ASTM D 2671		
Sizes 3/64 through 1/2 Sizes 3/4 through 2	kV/mm	500 minimum (19.700)			
Tensile strength	psi (MPa)	5000 minimum (34.5)	ASTM D 2671, 2"/minute		
Heavy metals analysis Cadmium, Mercury, Lead, Bismuth, Antimony	ppm	1 maximum (total of all metals)	USP XXII Physiochemical tests-plastic (Note 1)		

*Denotes lot acceptance testNote

1: Sample preparation and extraction is per USP XXII. Metals analysis may be colorimetric as described in USP XXII or by equivalent quantitative analytical method.

TE.com/medical

TE Connectivity, TE connectivity (logo), Raychem and TE are trademarks owned or licensed by the TE Connectivity Ltd. family of companies.

All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warrantes regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2024 TE Connectivity. All Rights Reserved.

11/24 med-mt-1000-hst-ss-en