RaySpool

Convenient packaging and dispensing system for heatshrinkable tubing

Electronics

Product Facts

₹ Тусо

- Easy to store
- Easy to dispense
- Well-suited for repairs
- Single wall and adhesivelined tubings
- Wide variety of colors, sizes and kits available
- Also available are RaySpool kits comprised of 6 sizes and supplied with a mounting rack
- Stand alone racks and packaging sets also available
- RoHS compliant



Applications

The RaySpool system offers a convenient packaging and dispensing option for a range of heat-shrinkable tubings. The tubing is supplied on small reels which are overboxed and feature a dispensing window allowing the tubing to be easily and readily accessed. The RaySpool system is a suitable method of storing and for use in the workshop, service vehicle or laboratory. A varied selection of tubings is offered which will cover a diverse range of

applications including electrical insulation, strain relief, cable bundling and environmental protection. RaySpool packaging is available for CGPT, LSTT and CGAT.

Installation

See individual product pages.

Operating Temperature Range

See individual product pages.

UK: 44-208-420-8341

Specifications/Approvals

www.tycoelectronics.com

are metric equivalents.

See individual product pages.

to change.

Available in: Americas Europe Asia Pacific 1-81 Catalog 9-1773447-9 Dimensions are shown for USA: 1-800-522-6752 South America: 55-11-2103-6000 Dimensions are in inches and Revised 01-09 millimeters unless otherwise Canada: 1-905-470-4425 Hong Kong: 852-2735-1628 reference purposes only. Mexico: 52-55-1106-0800 Japan: 81-44-844-8013 specified. Values in brackets Specifications subject

C. America: 57-1-254-4444

RaySpool (Continued)

CGPT 2:1 Product Dimensions		Inside Diameter		Recovered Wall Thickness*			
	Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	After Heating	Spool Quantity - Black (meters)	Spool Quantity - Green/Yellow (meters)	Ordering Description
	1.6/0.8	1.6 (0.062)	0.8 (0.031)	0.45 ± 0.12	10.0	-	CGPT-R-1.6-col code
	2.4/1.2†	2.4 (0.093)	1.2 (0.046)	0.50 ± 0.12	10.0	-	CGPT-R-2.4-col code
	3.2/1.6†•	3.2 (0.125)	1.6 (0.062)	0.50 ± 0.12	10.0	5.0	CGPT-R-3.2-col code
	4.8/2.4†	4.8 (0.187)	2.4 (0.093)	0.50 ± 0.12	9.0	-	CGPT-R-4.8-col code
	6.4/3.2†•	6.4 (0.250)	3.2 (0.125)	0.65 ± 0.15	8.0	3.5	CGPT-R-6.4-col code
	9.5/4.8•	9.5 (0.375)	4.8 (0.187)	0.65 ± 0.15	6.0	3.0	CGPT-R-9.5-col code
	12.7/6.4†•	12.7 (0.500)	6.4 (0.250)	0.65 ± 0.15	6.0	2.5	CGPT-R-12.7-col code
	19/9.5•	19.0 (0.748)	9.5 (0.375)	0.75 ± 0.15	5.0	2.0	CGPT-R-19.0-col code
	25.4/12.7†•	25.4(1.000)	12.7 (0.500)	0.90 ± 0.20	3.0	1.5	CGPT-R-25.4-col code
	KIT CONTA	INS SIZES INI	DICATED BY †				CGPT-R-KIT-2

*Wall thickness will be less if tubing recovery is restricted during shrinkage.

Ordering Information

Color	Standard	Black (-0) Green/yellow (-45) available in sizes indicated by •
Size selection	Always order the largest size	that will shrink snugly over the component to be covered.
Standard packaging	On mini spools.	
Ordering description	See above for description	

CGPT 3:1 Product Dimensions		Inside [Inside Diameter			
	Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	After Heating	Spool Quantity (meters)	Ordering Description
	3/1†	3.0 (0.118)	1.0 (0.040)	0.55 ± 0.12	10.0	CGPT-R-3/1-col code
	6/2†	6.0 (0.236)	2.0 (0.079)	0.65 ± 0.12	7.0	CGPT-R-6/2-col code
	9/3†	9.0 (0.354)	3.0 (0.118)	0.75 ± 0.15	5.0	CGPT-R-9/3-col code
	12/4†	12.0 (0.472)	4.0 (0.157)	0.75 ± 0.15	4.0	CGPT-R-12/4-col code
	18/6†	18.0 (0.709)	6.0 (0.236)	0.85 ± 0.15	3.0	CGPT-R-18/6-col code
	24/8†	24.0 (0.945)	8.0 (0.315)	1.00 ± 0.20	3.0	CGPT-R-24/8-col code
	KIT CONTA	INS SIZES INDICAT	ED BY † (black only	')		CGPT-R-KIT-1

Ordering Information

Color	Standard	Black (-0) Red (-2) Yellow (-4) Blue (-6)
Size selection	Always order the lar	rgest size that will shrink snugly over the component to be covered.
Standard packaging	On mini spools.	
Ordering description	See above for desc	ription

1-82

Catalog 9-1773447-9 Revised 01-09

www.tycoelectronics.com are

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-208-420-8341

RaySpool (Continued)

LSTT 2:1 Product Dimensions

Inside Diameter		Recovered Wall Thickness*			
Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	After Heating	Spool Quantity - Black (meters)	Ordering Description
2.4/1.2†	2.4 (0.093	1.2 (0.046)	0.55 ± 0.12	10.0	LSTT-R-2.4-0
3.2/1.6†	3.2 (0.125)	1.6 (0.062)	0.55 ± 0.12	10.0	LSTT-R-3.2-0
4.8/2.4†	4.8 (0.187)	2.4 (0.093)	0.55 ± 0.12	9.0	LSTT-R-4.8-0
6.4/3.2†	6.4 (0.250)	3.2 (0.125)	0.65 ± 0.15	8.0	LSTT-R-6.4-0
9.5/4.8	9.5 (0.375)	4.8 (0.187)	0.65 ± 0.15	6.0	LSTT-R-9.5-0
12.7/6.4†	12.7 (0.500)	6.4 (0.250)	0.65 ± 0.15	6.0	LSTT-R-12.7-0
19/9.5	19.0 (0.748)	9.5 (0.375)	0.80 ± 0.15	5.0	LSTT-R-19.0-0
25.4/12.7†	25.4(1.000)	12.7 (0.500)	0.95 ± 0.18	3.0	LSTT-R-25.4-0
KIT CONTAIN	NS SIZES INDICAT	ED BY † (black only))		LSTT-R-KIT-1

*Wall thickness will be less if tubing recovery is restricted during shrinkage.

Ordering Information

Color	Standard	Black (-0)
Size selection	Always order the large	est size that will shrink snugly over the component to be covered.
Standard packaging	On mini spools.	
Ordering description	See above for descript	tion

CGAT 3:1 Product Dimensions		Inside Diameter		Recovered Wall Thickness*		
	Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	After Heating	Spool Quantity (meters)	Ordering Description
	3/1†	3.0 (0.118)	1.0 (0.040)	1.00 ± 0.25	5.0	CGAT-R-3/1-0
	6/2†	6.0 (0.236)	2.0 (0.079)	1.00 ± 0.25	3.5	CGAT-R-6/2-0
	9/3†	9.0 (0.354)	3.0 (0.118)	1.35 ± 0.25	3.0	CGAT-R-9/3-0
	12/4†	12.0 (0.472)	4.0 (0.157)	1.50 ± 0.25	2.5	CGAT-R-12/4-0
	18/6†	18.0 (0.709)	6.0 (0.236)	1.70 ± 0.25	2.0	CGAT-R-18/6-0
	24/8†	24.0 (0.945)	8.0 (0.315)	1.90 ± 0.25	1.5	CGAT-R-24/8-0
	KIT CONTA	INS SIZES INDICAT	ED BY † (black only)			CGAT-R-KIT-1

Ordering Information

Color	Standard Black (-0)
Size selection	Always order the largest size that will shrink snugly over the component to be covered.
Standard packaging	On mini spools.
Ordering description	See above for description

Catalog 9-1773447-9 Revised 01-09

www.tycoelectronics.com are

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 52-55-1106-0800 C. America: 57-1-254-4444