

MINIATURE QUICK CHANGE APPLICATION
END FEED HEAVY DUTY

AMP OF GREAT BRITAIN LIMITED

TERMINALS

NO	DESCRIPTION	REQ	PART NO.	NO.	DESCRIPTION	REQ	PART NO.	CRIMPING DATA			
1	CRIMPER WIRE	0	576122-3	43	WASHER LAMINATED	1	576122	TO APPLY TERMINAL			
2	SPACER INSULATION	0	1-576589-4	44	RAM	1	455674-1				
3	CRIMPER INSULATION	0	1-456134-4	45	PLUG NYLON	1	690191-1	PAD DIM	CRIMP HT.	WIRE SIZE	160100
4	SPACER TUBULAR	0	238009-1	46		0		A	.076	1.5mm	160101
5	SPACER SHEAR BLADE	0	1-240641-0	47		0		B	.073	1.0mm	160102
6	HOLD DOWN TERMINAL	0	1-	48	CAM	1	576179-3	C	.070	0.75mm	160108
7	BLADE SLUG	0	1-690474-0	49	BOLT CRIMPER	1	7-21002-9	D	.067	0.50mm	160340
8	ANVIL	0	1-240655-7	50		0		CRIMP	SIZE	TYPE	FEED
9	PLATE FRONT SHEAR	0	1-690482-8	51		0		WIRE	.110	F	160342
10	SPACER SHEAR PLATE	0	2-	52	LEVER TERMINAL	1	240634-1	INSUL.	.140	F	160351
11	PLATE REAR SHEAR	0	1-240644-1	53	FINGER FEED	1	576123	INSUL. RANGE		WIRE RANGE	
12	SPRING HOLD DOWN	0	1-	54	SPRING FEED FINGER	1	691499-1	.080 - .120		0.5 - 1.5mm	
13	SPACER HOLD DOWN	0	1-	55	PIN FEED FINGER	1	240624-1	EXPLODED VIEW		SET UP GAUGE	
14		0	-	56		0		REMARKS A-O-L Based on 677546-1. 			