1 Do not connect the USB cable until you are instructed to.

Ne connectez pas le câble USB tant que vous n'y êtes pas invité.

Schließen Sie das USB-Kabel erst an, wenn Sie dazu aufgefordet werden.

Sluit de USB-kabel pas aan wanner dit in de instructies wordt aangegeven.

Non collegare il cavo USB fino a quando non espreeamente richiesto.

No conecte el cable USB hasta que se le indique.

Ligue apenas o cabo USB quando isso lhe for solicitado

在您得到指示之前,请勿连接 USB 电缆

2 Access Printer driver from TE.com.

Accédez au pilote d'imprimante à partir de TE.com.

Greifen Sie auf den Druckertreiber von TE.com zu.

Open het printerstuurprogramma vanaf TE.com.

Accedere al driver della stampante da TE.com.

Acceda al controlador de la impresora desde TE.com.

Acesse o driver da impressora em TE.com.

从 TE.com 访问打印机驱动程序。

3 Install.

Installer.

Installieren.

Installere.

Installare.

Instalar.

安装

4 Connect and plug in. Turn on.

Connectez et branchez. Merttez sous tension.

Anschließen und einstecken, Einschalten.

Aasluiten en stekker in stopcontact. Inschakelen.

Connetterre e collegare alle presa. Accendere.

Conecte y enchufe. Encender.

Ligue à impressora e à corrente. Ligar

连接及插入电源线。启动。









5 Install printer on PC.

Installer l'imprimante sur PC.

Drucker auf dem PC installieren.


Printer op pc installeren.

Installa la stampante sul PC.

Instalar impresora en PC.

Instalar impressora no PC.

在电脑上安装打印机



6 Connect to your PC.

Reliez l'appareil à votre PC.

Ihren PC anschließen.

Aansluiten op uw pc.

Collegare al PC.

Conectar al ordenador.

Conectar ao PC.

连接到您的电脑

7 Loading path for ribbon.

Chemin de chargement du ruban.

Farbband-Zuführungsweg.

Laadpad voor lint.

Percorso di caricamento del nastro.

Colocar el recorrido de la cinta.

Colocação da fita de impressão.

加载碳带

8 Loading path for media.

Chemin de chargement des consommables.

Medien-Zuführungsweg.


Laadpad voor media.


Percorso di caricamento del supporto stampabile.


Colocar el material a ser impreso.

Colocação do material para impressão

加载耗材









5375 (08/13)

411-121061 CLASS 1-Public

T3212 & T3224 Printer Quick Start Guide

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners. The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

The information contained within this document is the property of TE Connectivity. It is supplied in confidence and the commercial security of the contents must be maintained. It must not be used for any purpose other than that for which it is supplied nor may any information contained in it be disclosed to unauthorised persons. It must not be reproduced in whole or in part without obtaining written permission from TE Connectivity (TE).

T3212 & T3224 Printer Warranty

The T3212 & T3224 Printers are warranted by TE Connectivity (TE) to be free from defect in material and workmanship

Proof of purchase and delivery date is required to validate the warranty period. The warranty becomes void if the equipment is modified, improperly installed or used, damaged by accident or neglect, or if any parts are improperly installed or replaced by the user.

NOTE: Products returned must be packaged in the original or comparable packing. In the event equipment is not so packaged, or if shipping damage is evident, it will not be accepted for service under warranty. If TE Connectivity determines that the product returned for warranty service or replacement is not defective as herein defined, the customer will pay all handling and transportation costs.

Printers: All printers are warranted against defect in material or workmanship for twenty-four (24) months from the delivery date.

Printheads: Since printhead wear is part of normal operation, the original printhead is covered by 24 months from purchase or up to 1 million printed idents (whichever comes first), using approved TE products and ribbons.

To qualify for this warranty, the printhead must be returned to TE Connectivity. If it is determined that the use of non-approved or inferior supplies has caused any defect in the printhead for which a warranty claim is made, the user is responsible for TE Connectivity labour and material charges required to repair the defect. Please refer to T3212 & T3224 technical datasheet TTDS-272 & 274 and the latest issue of the Identification printer product ribbon matrix (411-121005) for approved media. The warranty becomes void if the printhead is physically worn or damaged; also, if it is determined that failure to follow the preventive maintenance schedule listed in the T3212 & T3224 Printer Operators Manual (412-121035) has caused defect in the thermal printhead for which a warranty claim is made. TE Connectivity recommends regular cleaning of the printhead in accordance with Thermal Transfer printer cleaning instructions (411-121037).

The warranties given are the only warranties given to you. No other warranties, express or implied, are given. TE Connectivity does not make any implied warranty of merchantability or fitness for a particular purpose in connection with its sale of products or services. While TE Connectivity desire is to be responsive to your specific needs and questions, TE Connectivity does not assume responsibility for any specific application to which any Products are applied, including, but not limited to, compatibility with other equipment. All statements, technical information, or recommendations relating to TE Connectivity Products are based upon tests believed to be reliable, but do not constitute a guaranty or warranty. TE Connectivity maximum liability for warranty claims is limited to the invoice price of the Product claimed defective. TE Connectivity does not assume responsibility for delays in replacement or repair of products. TE Connectivity shall not under any circumstances whatsoever be liable to you or any other party for loss or profits, lost data, diminution of good will, or any other special or consequential damages whatsoever with respect to any warranty claim made by you. Specifically for software. TE Connectivity is not liable for any incidental or consequential damages caused by abuse or misapplication of the software or by its use in violation of the U.S. copyright law or international treaty.

No salesperson, representative, or agent of TE Connectivity is authorized to make any guaranty, warranty, or representation that contradicts the foregoing. Any waiver, alteration, addition, or modification to the foregoing warranties must be in writing and signed by an executive officer of TE Connectivity to be valid.

©2023 Tyco Electronics Corporation, a TE Connectivity Ltd. company All Rights Reserved | Indicates Change Rev [4] Class I Data Classification - See Policy TEC-02-04

21 September 2023