

General Attributes**Status: Released**

Specification number 53711
 Specification revision level J
 Specification revision date 03/31/1994
 CSR number 8354D
 CSR revision level B
 Owner AMP UNITED STATES
 CSR document part indicator CSR document

CSR Document Text

CSR document text

For AMP USA orders only:

Packaging is in accordance with AMP specifications 107-24 and 107-64 on file in the Sigmaform QC area.

Marking Requirements:

Mark Product with 0.25 inch high characters in WHITE ink:

" AMP Date Code " , and
 ".750 - .220 / 19 mm - 5.6 mm"

Repeat every 8 inches on opposite sides

Corporate Specification: SST / SST-FR revision B
 QC: Measure to SCD and for dimension A (our length):

Dash Number	AMP Requirement
53711-1	3.000 +/- 0.190 inches
53711-2	4.000 +/- 0.190 inches
53711-3	6.000 +/- 0.190 inches
53711-4	9.000 +/- 0.190 inches
53711-5	12.000 +/- 0.190 inches 25 piece kit of 1-53711-4
53711-6	18.000 +/- 0.250 inches (obsolete)
53711-7	24.000 +/- 0.250 inches (obsolete)
53711-8	1.500 +/- 0.130 inches
53711-9	2.000 +/- 0.130 inches
1-53711-0	48.00 - 49.00 inches
1-53711-3	12.000 +/- 0.250 inches 25 piece kit of 1-53711-4 (obs)
1-53711-4	12.000 +/- 0.190 inches
1-53711-5	12.000 +/- 0.190 inches (obsolete)
1-53711-6	3.000 +/- 0.190 inches (obsolete)
1-53711-7	7.000 +/- 0.190 inches (obsolete)
1-53711-8	9.000 +/- 0.190 inches (obsolete)
2-53711-1	50.00 - 51.00 inches (obsolete)
2-53711-2	48.00 - 49.00 inches (obsolete)
8-53711-3	6.000 +/- 0.190 inches; 2 piece kit of 53711-3
8-53711-4	3.000 +/- 0.190 inches; 1000 piece kit of 53711-1

EXCEPTIONS:

**** None ****

Manufacturing Attributes