

TruBlue Data Loggers



Image	Model Number	Accuracy	Range	Memory	Body Material	Nose Cap	Pressure Reference	Cable Options	List Price
	565 LEVEL	±0.01 Ft Meets USGS OSW Spec	0-22 PSI	8 MB	316 SS or Titanium	Ported	Vented	853 Interface Cable	SS \$995 Ti \$1,145
	555 LEVEL	±0.05% TEB	0-300 PSI	8 MB	316 SS or Titanium	Ported	Vented or Absolute	852 SS Suspension cable -OR- 853 Interface Cable	SS \$670 Ti \$825
	585 CTD	±0.05% TEB; 1% of Reading	0-300 PSI; 5 – 200K µS/cm	8 MB	316 SS or Titanium	Ported	Vented or Absolute	852 SS Suspension cable -OR- 853 Interface Cable	SS \$1,245 Ti \$1,295
	255 LEVEL	±0.05% TEB	0-300 PSI	8 MB or 56 MB*	316 SS or Titanium	Ported	Absolute	852 SS Suspension cable -OR- 853 Interface Cable	SS \$410 Ti \$565 * +\$135
	275 BARO	±0.05% TEB	8 –16 PSI	8 MB	316 SS or Titanium	Ported	Absolute	852 SS Suspension Cable	SS \$410 Ti \$565
	285 CT	1% of Reading	5 – 200K µS/cm	8 MB	316 SS or Titanium	Ported	N/A	852 SS Suspension cable -OR- 853 Interface Cable	SS \$795 Ti \$950

TruBlue Accessories



Field Cables



853-XXXXX
Interface Cable Assembly



852-XXXXX
Suspension Wire



Communication Cables



- 850-00855
Technician's Cable
- 850-00856
USB to Hirose Cable
- 850-00858
Hirose to Flying Leads Cable



850-00857
USB to Backshell
Programming Cable



Accessories



850-00805
Backshell



850-00800,
Removable Plug



850-00805
Auxiliary Battery



852-00005
Backshell for Battery



860-00825
Anti-Fouling Screen