

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ End Sections

## General Information

<b>Extended Product Type:</b>	EK10
<b>Product ID:</b>	1SNK710910R0000
<b>EAN:</b>	3472597109102
<b>Catalog Description:</b>	EK10 End Section - Dark Grey
<b>Long Description:</b>	- Compatible with ZK10, ZK10-PE, ZK16 and ZK16-PE PI-Spring screwless terminal blocks.

## Ordering

<b>Color:</b>	Dark Grey
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	39269097

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160027C0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	2 mm
<b>Product Net Height:</b>	80.5 mm
<b>Product Net Depth / Length:</b>	41.7 mm
<b>Product Net Weight:</b>	3.3 g

## Technical

<b>Spacing:</b>	2 mm
<b>Function:</b>	End Sections
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
<b>Suitable For:</b>	ZK10 ZK10-PE ZK16 ZK16-PE

## Technical UL/CSA

**Flammability According to UL94:** V0

## Environmental

**Ambient Air Temperature:** Operation -55 ... +110 °C  
Storage -55 ... +110 °C

**RoHS Status:** Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

**Instructions and Manuals:** 1SNK160027C0201

**RoHS Information:** 1SND230535F0201

## Classifications

**Object Classification Code:** X

## Container Information

**Package Level 1 Units:** 20 piece

**Package Level 1 Width:** 130 mm

**Package Level 1 Depth / Length:** 280 mm

**Package Level 1 Height:** 0 mm

**Package Level 1 Gross Weight:** 0.085 kg

**Package Level 1 EAN:** 3472597109102

**Package Level 2 Units:** 1800 piece

**Package Level 2 Width:** 300 mm

**Package Level 2 Depth / Length:** 300 mm

**Package Level 2 Height:** 400 mm

**Product Packing Type:** Bag

