





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER E.O. P18603	6-29-04	-	RDR
	A1	DRAWING UPDATED	12MAR2024	RK	CB



4 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A = JANUARY.
YEAR IS REPRESENTED BY LAST NUMERIC DIGIT. EX: 2 = 2002.

3 MATERIAL: HOUSING: PLASTIC, GROMMET: RUBBER.

2 THIS RECEPTACLE MATES WITH DTHD06-1-12S-XXXX PLUG.
(**** = ALL MODIFICATIONS)

1 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTIC
SEE ENVELOPE DRAWING 0425-015-0000.

NOTES: UNLESS OTHERWISE SPECIFIED.

WIRE INSULATION DIA		
CONTACT SIZE	MINIMUM O.D.	MAXIMUM O.D.
12	.134 [3.40]	.170 [4.32]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TOMSA DEC-30-02					
DIMENSIONS: INCHES [mm]		CHK -					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME RECEPTACLE #12 HD CONTACT DTHD SERIES COLOR: BLACK				
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±.025 [.64] 4 PLC ±- ANGLES ±0°30'0"		PRODUCT SPEC 108-151020					
MATERIAL		APPLICATION SPEC 114-151020	SIZE A3	CAGE CODE 00779	DRAWING NO C-DTHD04-1-12P	RESTRICTED TO -	
FINISH -		WEIGHT -	CUSTOMER DRAWING; RESTRICTED CUSTOMER		SCALE 3:1	SHEET 1 OF 1	REV A1