


.5MM FREE HEIGHT CONNECTORS

Two-Piece, Open Pin Field Connectors Designed For Parallel Stacking Board-to-Board Applications



Free height connectors are two-piece, open pin field connectors designed for use in parallel stacking board-to-board applications. The free height connector grouping consists of vertical board-mount receptacles and plug assemblies. TE Connectivity (TE) offers these connectors in various combinations of plug and receptacle height, providing design flexibility with the ability to vary the spacing between parallel boards. The .5mm free height connector features a range of position sizes and are packaged for easy assembly.


INTRODUCTION TO THE .5MM FREE HEIGHT CONNECTOR

The PICMG COM Express standard specifies .5mm free height as the module-to-carrier card interface.




PITCH

Pitch refers to the spacing between pin or receptacle centerlines.



STACKING HEIGHTS

.5mm: 5mm, 6mm, 8mm



POSITIONS

.5mm: 220, 240, and 440 positions

FEATURES

- Allows for high pin counts in a small footprint to save PC board real estate
- Available in 220, 240, and 440 position configurations
- Offered in a variety of stacking heights, ranging from 5mm to 8mm
- Available on tape-and-reel packaging for lead protection and automated placement
- Compatible with standard pick-and-place vacuum nozzles
- Available with UL and RoHS compliant parts

APPLICATIONS

- Home security devices
- Consumer electronics
- Data storage devices
- Telecommunications
- Automotive dashboard controls
- Customized PC boards
- Industrial computing devices
- Anywhere high-density stacking is desired

.5MM FREE HEIGHT CONNECTORS

.5MM FREE HEIGHT PART NUMBER SELECTION GUIDE

			PLUG										
			PN	3-1827253-6	3-1827233-6	3-5353652-6	9-1939756-6#	3-1939756-6*	3-6318491-6	3-2040713-6*#	8-6318491-6	9-6318491-6*#	3-5353614-7#
			H	5	5	8	8	8	8	8	8	8	6
RECEPTACLE	PN	H	Pos	220	440	440	220	220	220	220	220	220	240
	3-6318490-6	4	220	5			8	8	8			8	
	3-1827231-6	4	440		5	8							
	3-1939755-6*	4	220	5			8	8	8			8	
	6-5353606-6#	4	220	5			8	8	8	8	8	8	
	3-5353606-7	4	240										6

* 30u" gold plating on contact interface

with a pickup cap

Stack Height

FOR MORE INFORMATION:

TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752
 Canada: +1 (905) 475-6222
 Mexico: +52 (0) 55-1106-0800
 Latin/S. America +54 (0) 11-4733-2200
 Germany: +49 (0) 6251-133-1999
 UK: +44 (0) 800-267666
 France: +33 (0) 1-3420-8686
 Netherlands: +31 (0) 73-6246-999
 China: +86 (0) 400-820-6015

For other country numbers, go to te.com/supportcenter

te.com

© 2015 TE Connectivity Ltd. All Rights Reserved. 1-1773863-5

TE, TE Connectivity and the TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

UL, RoHS, and PICMG COM Express are trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

