SPECIFICATION CONTROL DRAWING

55A7526


Title

TWO CONDUCTOR CABLE, TIN-COATED COPPER CONDUCTOR, UNSHIELDED, UNJACKETED

Date 07-15-04

Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55A



CABLE CONSTRUCTION DETAILS				
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT
		NOMINAL	MAXIMUM	(lbs/1000 ft)
55A7526-18-*	18	.140	.146	14.7

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C
Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
INSULATION FLAWS:
Spark Test, 5.7 kV (rms) at 3kHz
Impulse Dielectric Test, 8.0 kV (peak)

The "*" in the part numbers above shall be replaced by color code designators with a slash separating component wire colors:

1/ Example: AWG 18, black and white component wires: 55A7526-18-0/9

NOTE: Nominal values are for information only Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "AXXX".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 1

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL.

tycoElectronics

Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-227-8816 Fax: 1-650-361-6297