
## SPECIFICATION CONTROL DRAWING

55PC022A

TITLE TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, 600 VOLT

Date 12-6-96 Revision

This specification sheet forms a part of the latest issue of Raychem Specifiction 55PC.



		CONSTRI	JCTION DET	AILS		
PART NUMBER	CONDUCTOR SIZE (AWG)	DIAMETER ( in.)			WEIGHT ( lbs/1000 ft. )	
		LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC
55PC022A-26-*	26	.069	.072	.075	2.94	3.14

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) INSULATION FLAWS: Impulse Dielectric Test, 8.0 kV (peak)

## PART NUMBER:

The "\*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors. Example: AWG 26, white and black component wires; 55PC022A-26-9/0

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

300 Constitution Drive, Menlo Park, California 94025 1-800-2 Raychem FAX: 1-415-361-829