

## 723 hter Receptacle angled rotatable

speedtec

insulation insert Code 1 (socket) Earth-to-Housing Connection according to VDE 0627 **Protection Against Contact according to VDE 0623 Electrically Protective Separation according to VDE 0140** flange mount /Flange 25x25

## **Technical Data**

number of pins power 7 (6+PE) signal

temperature range -20 °C to 130 °C

protection type when connected IP 66/67

330 rotation range

**Electrical Data** 

power signal max. 25 A\* max. 1.2 A\* 850V/DC 630V/AC 50 V (DC) rated current rated voltage rated insulation voltage (L-L) 6000 V 1500 V

mating cycles 500

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category max. height for operation 2000 m

Material

zinc diecast / chromated housing insulation insert PA 6.6 mod., UL 94/V0

seals

Contacts (not part of product contents)

**Tools** (not part of product contents)

H 56 C 204 NN 00 00 0200 000 H G C 204 N 00 00 0200 000







© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedted

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz



