MHHT-3-5K2-G-101 MARINE HIGH VOLTAGE HEAT SHRINKABLE TERMINATION KIT

Components List:

ITEM NUMBER	DESCRIPTION	QTY	U/M
1	Heat shrinkable tubing, 40"	6	PC
2	Heat shrinkable breakout Boot	1	PC
3	Sealant Mastic, red, 15" length.	6	PC
4	Stress Relieving Mastic (SRM), yellow, 24 " long	6	PC
5	SRM wedge for crotch, yellow	1	PC
6	Roll spring clamp	1	PC
7	Ground Braid, #4 AWG, 24" length	1	PC
8	Copper tape, 3/8" width, 8" length each	3	PC
9	Discharge control compound (grease) or DCC	2	PC
10	Copper mesh tape, 2" width	1	PC
11	Cable cleaning preparation kit	1	EA
12	Installation instructions (See note 2)	1	EA

Notes:

- 1. For use with 250 MCM or 400 MCM custom military marine cable: stranded, silicone insulated, flooded, with ground wires, an overall braided shield and low smoke cross-linked polyolefin jacketed.
- 2. Refer to TUS-41-3027 for installation instructions.

CUSTOMER DRAWING

Tyco Electro		Raychem Molded Parts 300 Constitution Drive Menlo Park, CA 94025 USA		MARINE HIGH VOLTAGE SHRINKABLE TERMINATION KIT			
TYCO ELECTRONICS RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION				Document No. MHHT-3-5K2-G-101			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE SHOWN IN BRACKETS				Rev.: B		Rev. Date: March 16, 2010	
DRAWN BY: UNGUYEN	CAGE CODE: 06090	Org. Date: 2/16/10	File name ECO-10-0		SCALE: None	SIZE: A	SHEET: 1 of 1