



REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
D		REV PER ECN-24-278474	05AUG2024	JAB JG
E		REV PER ECN-24-282911	06SEP2024	LP JG

WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).



CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B 45 MAX	SILVER PLATE PER ASTM B700
O RING	SILICONE RUBBER PER A-A-59588	N/A
FEMALE CONTACT	BeCu PER ASTM B196	GOLD PLATE PER ASTM B488
CONTACT CRIMP BARREL	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488
GASKETS	SILICONE RUBBER PER A-A-59588	N/A
BUSHING	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
OUTER CONTACT	BeCu PER ASTM B196	SILVER PLATE PER ASTM B700
SPLIT WASHER	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
COUPLING NUT	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
SPRING WASHER	BeCu PER ASTM B194	SILVER PLATE PER ASTM B700
HALF WASHER	BRASS PER ASTM B16	NICKEL PLATE PER SAE-AMS-QQ-N-290
CENTER CONTACT	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
RIGHT ANGLE SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRICS	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
INNER FERRULE	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
COMPONENT	MATERIAL	FINISH

RECOMMENDED CABLE PREPARATION



NOTES:
 1. PART NO "132391-1 & DATE CODE ON INDICATED SURFACE".
 2. FOR USE ON CABLE RG 55B/U 142B/U 223/U 400/U & KX23.

220045-2	132391-1
CRIMP TOOL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

TE Connectivity

RIGHT ANGLE PLUG WEATHERPROOF

SCALE 4:1 SHEET 1 OF 1 REV E