


P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		Update drawing	11MAR2009	MS	DB

1392020-1 AS SHOWN



- STANDARD: ACCORDING TO DIN 41626, PART 2
- SPRING CONTACT: BERYLLIUM - COPPER
- CONTACT PLATING: GOLD
- DIELECTRIC: PTFE
- FULL CRIMP CENTER CONTACT: SQ 0.7
OUTER CONDUCTOR: HEX 3.2



General tolerances ISO 2768-mH.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		27SEP00		Tyco Electronics	
K.Donnet		27SEP00		Lugano - Switzerland	
CHK		K.Mattheeuws		NAME	
APVD		-		COAX INSERT CABLE JACK FOR	
PRODUCT SPEC		-		CABLE RG 316 / RG 174 / RG 188	
APPLICATION SPEC		114-90006		DIN 1.0 / 2.3	
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO	
-		-		A3 00779 C=1392020	
ANGLE		WEIGHT		RESTRICTED TO	
0 PLC ± [±] _±		-		-	
1 PLC ± [±] _±		-			
2 PLC ± [±] _±		-			
3 PLC ± [±] _±		-			
4 PLC ± [±] _±		±2°			
CUSTOMER DRAWING		SCALE		10:1	
		SHEET		1 OF 1	
		REV		A1	