



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
1589468-1	1589468	SSM005L85HN	Dualobe, 1 row, metal, 5 position, receptacle w/integrated standoffs, vertical mount, surface termination, 2 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589468-2	1589468	SSM009L85HN	Dualobe, 1 row, metal, 9 position, receptacle, w/integrated standoffs, vertical mount, surface termination, 2 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589468-3	1589468	SSM015L85HN	Dualobe, 1 row, metal, 15 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 2 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589468-4	1589468	SSM037L85PQ	Dualobe, 1 row, metal, 37 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 2 side exit, .040 extended leads, tin/lead leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
1589468-5	1589468	SSM015L85IQ	Dualobe, 1 row, metal, 15 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 2 side exit, .040 extended leads, tin/lead leadframe, 1.2 x .200 mounting screw, thread for 1.2 jackscrews.
1589468-6	1589468	SSM015L85LQ	Dualobe, 1 row, metal, 15 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 2 side exit, .040 extended leads, tin/lead leadframe, 1.2 x .200 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.