



| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
| | E | REVISED PER ECR-20-004823 | 01APR2020 | GK | MN |

NOTES:

- 1 RANGE: $\phi 21$ MAX.
- 2 MIN. TENSILE STRENGTH 82N.



| | | | |
|------|---------|---------------|-------------|
| 1000 | BLACK | POLYAMIDE 6.6 | 4-160967-2 |
| 1000 | NATURAL | POLYAMIDE 6.6 | 4-160967-1 |
| 100 | BLACK | POLYAMIDE 6.6 | 2-160967-2 |
| 100 | NATURAL | POLYAMIDE 6.6 | 2-160967-1 |
| QTY | FINISH | MATERIAL | PART NUMBER |

| | | | | | |
|---|--|-----------------------------------|-------------------|--------------------|------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 01APR2020 GOPALAKRISHNA HV | TE Connectivity | | |
| | | CHK 01APR2020 GOPALAKRISHNA HV | | | |
| | | APVD 01APR2020 M. NUTTALL | NAME CABLE TIE | | |
| DIMENSIONS: mm | | PRODUCT SPEC - | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APPLICATION SPEC - | | | |
| 0 PLC ± - 1 PLC ± 0.4 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - | | SIZE A3 | | CAGE CODE 00779 | DRAWING NO C-160967 |
| MATERIAL SEE TABLE | | WEIGHT - | | RESTRICTED TO - | |
| FINISH SEE TABLE | | CUSTOMER DRAWING | | | |
| | | | SCALE NTS | SHEET 1 OF 1 | REV E |