




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-				
E1		ECR-08-014314	25-09-08	AEG	WRV



OPTIONAL (2x)



SECTION A-A

MATERIAL: HOUSING, 2.07, 90% GLASS FIBER
CONTACT: PH. BR, THT-LEAD (SS / 7) PLATING

OBSOLETE

ORDER NUMBER	NUMBER OF POSITIONS	2" MAX. M.M.	2" MAX. INCH.
161701_2	2	10.1	.398
-3	3	15.1	.594
-4	4	20.1	.791
-5	5	25.1	.988
-6	6	30.1	1.185
-7	7	35.1	1.382
-8	8	40.1	1.579
-9	9	45.1	1.776
L -0	10	50.1	1.973
L -1	11	55.1	2.169
L -2	12	60.1	2.366
-3	13	65.1	2.563
-4	14	70.1	2.760
L 161701_5	15	75.1	2.957

SEE TABLE	SEE ABOVE	SEE ABOVE
ORDER NO.	MATERIAL	PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17APR81	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
DIMENSIONS: mm		CHK -	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 21PAR81	2_15 POS. FEMALE ON WIRE CONNECTOR ASS'Y (VERTICAL) FOR MINI-MATCH INTERCONNECTION PITCH 5.0 mm.	
0 PLC ± -		PRODUCT SPEC -	SIZE	RESTRICTED TO
1 PLC ± -		APPLICATION SPEC -	CAGE CODE	
2 PLC ± -		WEIGHT -	DRAWING NO	
3 PLC ± -		A3 00779 C-161701		
4 PLC ± -		CUSTOMER DRAWING		
ANGLES ± -		SCALE	SHEET	REV
FINISH -		NTS	1 OF 1	E1