



パネル取付穴寸法

注:

1. 適用9-ミナシは 61115, 61117
2. 嵌合するキャップハウジングは 170895
3. 適用板厚は 0.8~1.65 mm とし角半径 R は 0.4R 以下
4. 取付穴打抜き方向とハウジング挿入方向は同じとする。

△ OBSOLETE

1	170094-9	△	黒	10
1	A	△	灰	9
1	-	△	灰	8
1	-	△	青	7
1	-	△	緑	6
1	-	△	黄	5
1	-	△	橙	4
1	-	△	赤	3
1	-	△	茶	2
	170894-1		自然色	1

F1	PER ECR-17-016055	JB	DZ	08NOV 2017
E	ADD'D (REV. E)	K.S.	J.L.	11/13
E1	REVISED (REV. E)	T.A.	K.C.	11/13
E	REVISED (REV. E)	K.S.	J.L.	11/13
D	ADD'D -1 ~ -0	K.S.	J.L.	11/13
C1	REVISED	K.S.	J.L.	11/13
C	REVISED (REV. B)	K.S.	J.L.	11/13
B	ADD'D CIRCUIT NO.	K.S.	J.L.	11/13
A	REDRAWN	K.S.	J.L.	11/13

C-170894

品名 (REQUIRED PER ASSEMBLY):		色 (COLOR):		摘要 (REMARKS):		ITEM NO.
66 ナイロン		自然色		顧客図面 (CUSTOMER COPY) (REFERENCE ONLY)		
DR. K. Kobayashi		WIRE RANGE:		TE Connectivity		
CHK. K. Shinai		WIRE INSULATION DIA.:		2-1		
DE. 11/13		TOLERANCE: ±0.4 EXCEPT AS NOTED		REV. NO. F1		
APPROV. 11/13		SCALE: 2-1		C-170894		
DESCRIPTION:		15ピンメイトロックプラグハウジング				

単位: 尺 DIMENSIONS IN MM. DO NOT SCALE PRINT