



#6-32 UNC-2B
ネジ穴、4ヶ所、

NOTE:

- 1 最大電線束線径：φ26。
最小電線束線径：φ17。
- 2 -1 絶縁スリーブなし
- 2 絶縁スリーブ(P/N 21330-4) 2ヶ添付
- 7-1 絶縁スリーブなし

- △ リベット(スチール、ニッケルメッキ)と固定側ケーブルクランプ(スチール、メッキ)を組み込んだもの。
- △ ウィスカー対策・RoSH対応品。

OBSOLETE

数量	品番 (NUMBER)	名称 (NAME)	摘要 (REMARKS)	ITEM NO.
1	3	CABLE CLAMP	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	3
1	2	SHIELD (RIGHT HALF)	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	2
1	1	SHIELD (LEFT HALF)	△ ZINC-COATED STEEL, PAINTED TO METALIC SILVER	1
2	2	#4-40 UNC-2A LENGTH 19.1REF	△ ZINC-COATED STEEL, ORGANIC COATING	5
2	2	#4-40 UNC-2A LENGTH 6.4REF	△ STAINLESS STEEL, ORGANIC COATING	4
1	3	CABLE CLAMP	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	3
1	2	SHIELD (RIGHT HALF)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	2
1	1	SHIELD (LEFT HALF)	ZINC-COATED STEEL, PAINTED TO METALIC SILVER	1

REV.	DESCRIPTION	BY	DATE	CHK.	DATE
G	REVISED PER ECO-20-007658	KR	MZ	12JUN 2020	
F	REVISED	T.N	N.Y.	09SEP 2013	
E	J-3982				
D	ECN J5-3770	KA	NO	9/13	
C	ADDED NOTE 2 (REV. E)	Y.T	NO	9/13	
B	REVISED (REV. D)	Y.T	NO	9/13	
A	REVISED (REV. B)	Y.T	NO	9/13	
Q	RELEASED (REV. A)	Y.T	NO	9/13	

C-171074

船立部品 (REQUIRED PER ASSEMBLY)		COPYRIGHT 2012 BY Tyco Electronics Japan G.K.		参考図面 (CUSTOMER COPY) (REFERENCE ONLY)	
材料 (MATERIAL)	適合電線範囲 (WIRE RANGE)	TE Connectivity			
仕上 (FINISH)	保護外皮径 (INSULATION DIA.)				
DR.	公差 (TOLERANCE EXCEPT AS NOTED)	尺法 (SCALE)	LOC	SIZE	番号 (NO)
CHK.	±0.4	1:1	J	B	C-171074
DE.					
APP.	名称 (NAME)	75極 180° 3-11ド			

単位：mm DIMENSIONS IN MM. DO NOT SCALE PRINT